

Cat® C4.4

Diesel Generator Sets



Standby & Prime: 50 Hz



Image shown might not reflect actual configuration

Engine Model	Cat® C4.4 Inline 4-stroke Diesel
Bore x Stroke	105.0 mm x 127.0 mm (4.1 in x 5.0 in)
Displacement	4.4 L (268.5 in³)
Compression Ratio	16.7:1
Aspiration	Turbocharged Air To Air Charge Cooled
Fuel Injection System	Inline
Governor	Electronic

Model	Standby	Prime	Emission Strategy
DE110E3	50 Hz	50 Hz	EU IIIA
	110.0 kVA (88.0 kW)	100.0 kVA (80.0 kW)	

PACKAGE PERFORMANCE


Performance	Standby	Prime
Frequency	50 Hz	50 Hz
Genset Power Rating	110.0 kVA	100.0 kVA
Genset power rating with fan @ 0.8 power factor	88.0 kW	80.0 kW
Emissions	EU IIIA	
Performance Number	P4522B	
Fuel Consumption		
Fuel Tank Capacity, litres (US gal)	250 (66.0)	
100% load with fan, L/hr (gal/hr)	24.6 (6.5)	23.4 (6.2)
75% load with fan, L/hr (gal/hr)	20.7 (5.5)	19.5 (5.2)
50% load with fan, L/hr (gal/hr)	15.6 (4.1)	14.6 (3.9)
Cooling System¹		
Radiator air flow, m³/min (CFM)	201.0 (7098)	
Total coolant capacity, L (gal)	17.0 (4.5)	
Inlet Air		
Max. Combustion Air Intake Restriction, kPa (in water)	5.0 (20.1)	
Combustion air inlet flow rate, m³/min (CFM)	6.7 (238)	6.4 (227)
Max. Allowable Combustion Air Inlet Temp, °C (°F)	50 (122)	
Exhaust System		
Exhaust stack gas temperature, °C (°F)	675 (1247)	657 (1215)
Exhaust gas flow rate, m³/min (CFM)	17.4 (614)	16.4 (580)
Exhaust system backpressure (maximum allowable), kPa (in water)	15.0 (4.4)	
Heat Rejection		
Heat rejection to jacket water, kW (BTU/min)	51.9 (2952)	47.1 (2679)
Heat rejection to alternator, kW (BTU/min)	7.8 (444)	
Heat rejection to atmosphere from engine, kW (BTU/min)	22.1 (1257)	20.0 (1137)

C4.4 Diesel Generator Sets Electric Power



Alternator ²							
Duty Cycle		Standby			Prime		
Phase		3-Phase			3-Phase		
Voltages, V		380/220	400/230	415/240	380/220	400/230	415/240
Current, Amps		167	159	153	152	144	139
Frame: LC3114F Excitation: SE	Temperature Rise, @ 40°C	256	240	220			
	Motor Starting Capability 30% Voltage Dip, skVA	153	159	167			
Frame: M2236L4 Excitation: SE	Temperature Rise, @ 40°C	163	163	163	125	125	125
	Motor Starting Capability 30% Voltage Dip, skVA	166	182	194	166	182	194

WEIGHTS & DIMENSIONS



Dim "A" mm (in)	Dim "B" mm (in)	Dim "C" mm (in)	Dry Weight kg (lb)
2089 (82.2)	1120 (44.1)	1495 (58.9)	1190 (2623)

Note: General configuration not to be used for installation. See general dimension drawings for detail.

APPLICABLE CODES AND STANDARDS:

AS1359, IEC60034-1, ISO 3046, ISO 8528, NEMA MG1-33, EAC, CE, UKCA.

Note: Codes may not be available in all model configurations. Please consult your Cat dealer for availability.

STANDBY: Output available with varying load for the duration of the interruption of the normal source power. Average power output is 70% of the standby power rating. Typical operation is 200 hours per year, with maximum expected usage of 500 hours per year.

PRIME: Output available with varying load for an unlimited time. Average power output is 70% of the prime power rating. Typical peak demand is 100% of prime rated kW with 10% overload capability for emergency use for a maximum of 1 hour in 12. Overload operation cannot exceed 25 hours per year.

RATINGS: Ratings are based on SAE J1349 standard conditions. These ratings also apply at ISO 3046 standard conditions.

DEFINITIONS AND CONDITIONS

¹ For ambient and altitude capabilities consult your Cat dealer. Air flow restriction (system) is added to existing restriction from factory.

² Generator temperature rise is based on a 40°C ambient per IEC60034-1.

www.cat.com/electricpower
©2025 Caterpillar
All rights reserved.

Materials and specifications are subject to change without notice.
The International System of Units (SI) is used in this publication.

CAT, CATERPILLAR, LET'S DO THE WORK, their respective logos, "Caterpillar Corporate Yellow", the "Power Edge" and Cat "Modern Hex" trade dress as well as corporate and product identity used herein, are trademarks of Caterpillar and may not be used without permission.