

# Cat® C27

## Diesel Generator Sets



Image shown may not reflect actual configuration.

Bore – mm (in)	137.2 (5.4)
Stroke – mm (in)	152.4 (6.0)
Displacement – L (in <sup>3</sup> )	27.03 (1649.47)
Compression Ratio	16.5:1
Aspiration	TA
Fuel System	MEUI
Governor Type	ADEM™ A4

Standby 60 Hz ekW (kVA)	Prime 60 Hz ekW (kVA)	Standby 60 Hz ekW (kVA)	Prime 60 Hz ekW (kVA)	Emissions Performance
750 (937)	680 (850)	800 (1000)	725 (906)	U.S. EPA Emergency Stationary Use Only (Tier 2)

### Standard Features

#### Cat® Diesel Engine

- Meets U.S. EPA Emergency Stationary Use Only (Tier 2) emission standards
- Reliable performance proven in thousands of applications worldwide

#### Generator Set Package

- Accepts 100% block load in one step and meets NFPA 110 loading requirements
- Conforms to ISO 8528-5 G3 load acceptance requirements
- Reliability verified through torsional vibration, fuel consumption, oil consumption, transient performance, and endurance testing

#### Alternators

- Superior motor starting capability minimizes need for oversizing generator
- Designed to match performance and output characteristics of Cat diesel engines

#### Cooling System

- Cooling systems available to operate in ambient temperatures up to 50°C (122°F)
- Tested to ensure proper generator set cooling

#### Cat Energy Control System (ECS) / GCCP

- User-friendly interface and navigation
- Multiple parameters are monitored & displayed simultaneously for full visibility
- The module can be configured to suit a wide range of applications for user flexibility

#### Warranty

- 24 months/1000-hour warranty for standby and mission critical ratings
- 12 months/unlimited hour warranty for prime and continuous ratings
- Complimentary 5-Year Platinum Cat® Extended Service Coverage (ESC) available on eligible products\*

#### Worldwide Product Support

- Cat dealers have over 1,800 dealer branch stores operating in 200 countries
- Your local Cat dealer provides extensive post-sale support, including maintenance and repair agreements

#### Financing

- Caterpillar offers an array of financial products to help you succeed through financial service excellence
- Options include loans, finance lease, operating lease, working capital, and revolving line of credit
- Contact your local Cat dealer for availability in your region

## Optional Equipment

### Engine

#### Air Cleaner

- Single element
- Dual element
- Heavy duty

#### Muffler

- Industrial grade (25 dB)

#### Starting

- Standard batteries
- Oversized batteries
- Standard electric starter(s)
- Jacket water heater

### Alternator

#### Output voltage

- 208V
- 240V
- 480V
- 600V

#### Temperature Rise (over 40°C ambient)

- 150 °C
- 125 °C
- 105 °C
- 80 °C

#### Winding type

- Random wound

#### Excitation

- Internal excitation (IE)

#### Attachments

- Anti-condensation heater
- Stator and bearing temperature monitoring and protection

### Power Termination

#### Type

- Bus bar
- Circuit breaker
- 400A     800A
- 1200A     1600A
- 2000A     2500A
- 3000A
- IEC     UL
- 3-pole     4-pole
- Manually operated
- Electrically operated

#### Trip Unit

- LSI     LSI-G
- LSI-G-P

### Factory Enclosure

- Sound attenuated

#### Attachments

- Cold weather bundle
- DC lighting package
- Motorized louvers

### Fuel Tank

#### Controller

- 1000 gal (3785 L)
- 2000 gal (7571 L)
- 3000 gal (1362 L)

### Control System

#### Controller

- GCCP 1.2
- CAT ECS 100
- CAT ECS 200

#### Attachments

- Local annunciator module
- Remote annunciator module
- Expansion I/O module
- Remote monitoring software

### Charging

- Battery charger – 10A
- Battery charger – 20A
- Battery charger – 30A

### Vibration Isolators

- Rubber
- Spring
- Seismic rated

### Telematics

#### Connectivity

- Ethernet
- Cellular
- Satellite

### Extended Service Options

#### Terms

- 2 year
- 3 year
- 5 year
- 10 year

#### Coverage

- Silver
- Gold
- Platinum
- Platinum Plus

### Ancillary Equipment

- Automatic transfer switch (ATS)
- Uninterruptible power supply (UPS)
- Paralleling switchgear
- Paralleling controls

### Certifications

- ULC 2200 Listed
- CSA
- IBC seismic certification
- OSHPD pre-approval


**Note:** Some options may not be available on all models. Certifications may not be available with all model configurations. Consult factory for availability.

**Package Performance**

<b>Performance</b>	<b>Standby</b>		<b>Prime</b>		<b>Standby</b>		<b>Prime</b>	
Frequency	60 Hz		60 Hz		60 Hz		60 Hz	
Genset power rating with fan	750 ekW		680 ekW		800 ekW		725 ekW	
Genset power rating with fan @ 0.8 power factor	937 kVA		850 kVA		1000 kVA		906 kVA	
Emissions	EPA ESE (Tier 2)		EPA ESE (Tier 2)		EPA ESE (Tier 2)		EPA ESE (Tier 2)	
Performance number	DM9071-03		DM9073-02		DM7696-02		DM9069-02	
<b>Fuel Consumption</b>								
100% load with fan – L/hr (gal/hr)	202.9	(53.6)	187.4	(49.5)	216.9	(57.3)	199.6	(52.7)
75% load with fan – L/hr (gal/hr)	162.4	(42.9)	149.6	(39.5)	171.7	(45.4)	157.8	(41.7)
50% load with fan – L/hr (gal/hr)	116.2	(30.7)	107.0	(28.3)	122.3	(32.3)	112.5	(29.7)
25% load with fan – L/hr (gal/hr)	70.6	(18.7)	66.0	(17.4)	73.9	(19.5)	69.0	(18.2)
<b>Cooling System</b>								
Radiator air flow restriction (system) – kPa (in. water)	0.12	(0.48)	0.12	(0.48)	0.12	(0.48)	0.12	(0.48)
Radiator air flow – m <sup>3</sup> /min (CFM)	1200	(42377)	1200	(42377)	1200	(42377)	1200	(42377)
Engine coolant capacity – L (gal)	55.0	(14.5)	55.0	(14.5)	55.0	(14.5)	55.0	(14.5)
Radiator coolant capacity – L (gal)	41.0	(10.0)	41.0	(10.0)	41.0	(10.0)	41.0	(10.0)
Total coolant capacity – L (gal)	96.0	(24.5)	96.0	(24.5)	96.0	(24.5)	96.0	(24.5)
<b>Inlet Air</b>								
Combustion air inlet flow rate – m <sup>3</sup> /min (CFM)	58.7	(2073.6)	56.0	(1977.7)	62.8	(2216.4)	60.3	(2129.4)
<b>Exhaust System</b>								
Exhaust stack gas temperature – °C (°F)	509.3	(948.7)	502.5	(936.5)	511.4	(952.5)	500.6	(933.0)
Exhaust gas flow rate – m <sup>3</sup> /min (CFM)	158.9	(5610.2)	149.7	(5285.5)	170.3	(6011.7)	160.7	(5674.4)
Exhaust system backpressure (maximum allowable) – kPa (in. water)	6.7	(27.0)	6.7	(27.0)	6.7	(27.0)	6.7	(27.0)
<b>Heat Rejection</b>								
Heat rejection to jacket water – kW (BTU/min)	324	(18441)	307	(17433)	330	(18785)	320	(18191)
Heat rejection to exhaust (total) – kW (BTU/min)	738	(41994)	693	(39387)	796	(45257)	741	(42135)
Heat rejection to aftercooler – kW (BTU/min)	139	(7898)	123	(6970)	162	(9235)	146	(8320)
Heat rejection to atmosphere from engine – kW (BTU/min)	110	(6249)	92	(5238)	110	(6240)	89	(5074)
Heat rejection from alternator – kW (BTU/min)	53	(3014)	47	(2644)	40	(2292)	37	(2081)
<b>Emissions* (Nominal)</b>								
NO <sub>x</sub> mg/Nm <sup>3</sup> (g/hp-h)	2637.1	(5.25)	2330.9	(4.68)	2580.0	(5.18)	2283.7	(4.61)
CO mg/Nm <sup>3</sup> (g/hp-h)	123.9	(0.25)	147.4	(0.29)	115.1	(0.23)	135.6	(0.27)
HC mg/Nm <sup>3</sup> (g/hp-h)	11.2	(0.03)	10.9	(0.02)	12.5	(0.03)	12.2	(0.03)
PM mg/Nm <sup>3</sup> (g/hp-h)	8.8	(0.02)	8.8	(0.02)	9.7	(0.02)	9.0	(0.02)
<b>Emissions* (Potential Site Variation)</b>								
NO <sub>x</sub> mg/Nm <sup>3</sup> (g/hp-h)	4065.0	(8.15)	3846.5	(7.71)	4079.2	(7.51)	3445.5	(6.91)
CO mg/Nm <sup>3</sup> (g/hp-h)	224.0	(0.45)	220.6	(0.44)	256.4	(0.48)	224.8	(0.45)
HC mg/Nm <sup>3</sup> (g/hp-h)	13.0	(0.03)	16.5	(0.04)	14.6	(0.03)	17.7	(0.04)
PM mg/Nm <sup>3</sup> (g/hp-h)	15.0	(0.04)	14.7	(0.04)	9.8	(0.02)	8.7	(0.02)

\*mg/Nm<sup>3</sup> levels are corrected to 5% O<sub>2</sub>. Contact your local Cat dealer for further information.

## Weights and Dimensions



Dim "A" mm (in)	Dim "B" mm (in)	Dim "C" mm (in)	Dry Weight kg (lb)
4674 (184.0)	1723 (67.8)	2162 (85.1)	6622 (14,600)

**Note:** For reference only. Do not use for installation design. Contact your local Cat dealer for precise weights and dimensions.

## Ratings Definitions

### Standby

Output available with varying load for the duration of the interruption of the normal source power. Average power output is 70% of the standby power rating. Typical operation is 200 hours per year, with maximum expected usage of 500 hours per year.

### Prime

Output available with varying load for an unlimited time. Average power output is 70% of the prime power rating. Typical peak demand is 100% of prime rated kW with 10% overload capability for emergency use for a maximum of 1 hour in 12. Overload operation cannot exceed 25 hours per year.

### Fuel Rates

Fuel rates are based on fuel oil of 35° API [16°C (60°F)] gravity having an LHV of 42,780 kJ/kg (18,390 Btu/lb) when used at 29°C (85°F) and weighing 838.9 g/liter (7.001 lbs/U.S. gal.)

### Applicable Codes and Standards

CSA C22.2 No 100-04, UL489, UL 2200, IBC, IEC 60034-1, ISO 3046, ISO 8528, NEMA MG1-22, NEMA MG1-33, and facilitates compliance to NFPA 37, NFPA 70, NFPA 99, NFPA 110.

**Note:** Codes may not be available in all model configurations. Site level review needed for NFPA70. Please consult your local Cat dealer for availability.

### Data Center Applications

- ISO 8528-1 Data Center Power (DCP) compliant per DCP application of Cat diesel generator set prime power rating.
- All ratings Tier III/Tier IV compliant per Uptime Institute requirements.
- All ratings ANSI/TIA-942 compliant for Rated-1 through Rated-4 data centers.

\*Coverage subject to terms and conditions. Eligibility criteria and program availability subject to change without notice. No additional warranty, representation, or obligation, express or implied, is created or extended beyond those expressly set forth in the relevant ESC terms.

[www.cat.com/electricpower](http://www.cat.com/electricpower)

©2025 Caterpillar  
All rights reserved.

Materials and specifications are subject to change without notice. The International System of Units (SI) is used in this publication.

CAT, CATERPILLAR, LET'S DO THE WORK, their respective logos, "Caterpillar Corporate Yellow", the "Power Edge" and Cat "Modern Hex" trade dress as well as corporate and product identity. used herein, are trademarks of Caterpillar and may not be used without permission.