Cat® C18 Diesel Generator Sets



Standby & Prime: 60 Hz



Image shown	might not	reflect actual	configuration
IIIIaye SHUWII	IIIIqiit iiot	Tellect actual	comingulation.

Engine Model	Cat® C18 In-line 6, 4-cycle Diesel
Bore x Stroke	145 mm x 183 mm (5.7 in x 7.2 in)
Displacement	18.1 L (1106 in³)
Compression Ratio	14.5:1
Aspiration	Turbocharged Air-to-Air Aftercooled
Fuel Injection System	MEUI
Governor	Electronic ADEM™ A4 – G3 Class* capable

Model	Standby	Prime	Emission Strategy	
C18	550 ekW, 688 kVA	500 ekW, 625 kVA	TIER II Non-Road	

PACKAGE PERFORMANCE

Performance	Standby	Prime		
Frequency	60) Hz		
Genset Power Rating	688 kVA	625 kVA		
Genset power rating with fan @ 0.8 power factor	550 ekW	500 ekW		
Emissions	TIER II I	TIER II Non-Road		
Performance Number	DM8517	DM8521		
Fuel Consumption				
100% load with fan, L/hr (gal/hr)	147.0 (38.8)	135.0 (35.6)		
75% load with fan, L/hr (gal/hr)	114.9 (30.3)	109.3 (28.8)		
50% load with fan, L/hr (gal/hr)	83.7 (22.1)	79.6 (21.0)		
25% load with fan, L/hr (gal/hr)	43.0 (11.3)	42.5 (11.2)		
Cooling System ¹				
Radiator air flow restriction (system), kPa (in. water)	0.12 (0.48)	0.12 (0.48)		
Radiator air flow, m³/min (CFM)	803 (28357)	803 (28357)		
Engine coolant capacity, L (gal)	20.8 (5.5)	20.8 (5.5)		
Radiator coolant capacity, L (gal)	61 (16)	61 (16)		
Total coolant capacity, L (gal)	82 (22)	82 (22)		
Inlet Air				
Combustion air inlet flow rate, m³/min (CFM)	46.3 (1634.9)	44.8 (1581.9)		
Max. Allowable Combustion Air Inlet Temp, °C (°F)	50 (121)	49 (120)		
Exhaust System				
Exhaust stack gas temperature, °C (°F)	520.6 (969.1)	501.5 (934.7)		
Exhaust gas flow rate, m³/min (CFM)	128.9 (4551.5)	121.5 (4290.4)		
Exhaust system backpressure (maximum allowable), kPa (in. water)	10.0 (40.0)	10.0 (40.0)		
Heat Rejection				
Heat rejection to jacket water, kW (BTU/min)	180 (10236)	166 (9441)		
Heat rejection to exhaust (total), kW (BTU/min)	595 (33837)	549 (31223)		
Heat rejection to aftercooler, kW (BTU/min)	141 (8019)	129 (7336)		
Heat rejection to atmosphere from engine, kW (BTU/min)	77 (4379)	69 (3941)		

LEHE1580-05 Page 1 of 3

C18 Diesel Generator Sets Electric Power



Emissions (Nominal) ²	Standby	Prime
NOx, mg/Nm³ (g/hp-hr)	2703.5 (5.5)	2454.0 (5.1)
CO, mg/Nm³ (g/hp-hr)	161.0 (0.3)	108.8 (0.2)
HC, mg/Nm³ (g/hp-hr)	4.6 (0.01)	4.6 (0.01)
PM, mg/Nm³ (g/hp-hr)	13.2 (0.03)	11.9 (0.03)


Alternator ³													
Duty Cycle		Standby				Prime							
Phase				3-Ph	nase			3-Phase					
Voltages*, V		208	220	240	380	480	600	208	220	240	380	480	600
Current, Amps		1908	1804	1654	1045	827	662	1735	1640	1504	949	752	601
Frame: LC6124G	Temperature Rise @ 40°C	150	150	130		130	130	125	125	105		105	105
Excitation: AREP	Motor Starting Capability @ 30% Voltage Dip, skVA	1335	1479	1729		1729	1731	1335	1479	1729		1729	1731
Frame: LC7024H	Temperature Rise @ 40°C						105						105
Excitation: AREP	Motor Starting Capability @ 30% Voltage Dip, skVA						2023						2023
Frame: LC7024J	Temperature Rise @ 40°C	105	105	105	130	105		80	80	80	105	80	
Excitation: AREP	Motor Starting Capability @ 30% Voltage Dip, skVA	1524	1694	1993	1283	1993		1524	1694	1993	1283	1993	
Frame: LC7024F	Temperature Rise @ 40°C					130						105	
Excitation: AREP	Motor Starting Capability @ 30% Voltage Dip, skVA					1633						1633	
Frame: LC6114G	Temperature Rise @ 40°C	150	130	130		130		125	105	105		105	
Excitation: SE	Motor Starting Capability @ 30% Voltage Dip, skVA		1236	1445		1445		1116	1236	1445		1445	


^{*}Note: 220V and 380V are additional offerings for the Latin America Market.

LEHE1580-05 Page 2 of 3



WEIGHTS & DIMENSIONS





Dim "A"	Dim "B"	Dim "C"	Dry Weight		
mm (in)	mm (in)	mm (in)	kg (lb)		
3477 (137)	1628 (64)	2102 (83)	4431 (9769)		

Note: General configuration not to be used for installation. See general dimension drawings for detail.

APPLICABLE CODES AND STANDARDS:

CSA C22.2 No 100-04, UL489, UL869, UL2200, IBC, IEC60034-1, ISO 3046, ISO 8528, NEMA MG 1-22, NEMA MG 1-33 and facilitates the compliance to NFPA 37, NFPA70, NFPA 99, NFPA110.

Note: Codes may not be available for all model configurations. Site level review needed for NFPA 70. Please consult your Cat Dealer for availability.

STANDBY: Output available with varying load for the duration of the interruption of the normal source power. Average power output is 70% of the standby power rating. Typical operation is 200 hours per year, with maximum expected usage of 500 hours per year.

PRIME: Output available with varying load for an unlimited time. Average power output is 70% of the prime power rating. Typical peak demand is 100% of prime rated ekW with 10% overload capability for emergency use for a maximum of 1 hour in 12. Overload operation cannot exceed 25 hours per year.

RATINGS: Ratings are based on SAE J1349 standard conditions. These ratings also apply at ISO 3046 standard conditions.

DEFINITIONS AND CONDITIONS

- ¹ For ambient and altitude capabilities consult your Cat dealer. Air flow restriction (system) is added to existing restriction from factory.
- ² Emissions data measurement procedures are consistent with those described in EPA CFR 40 Part 89, Subpart D & E and ISO8178-1 for measuring HC, CO, PM, NOx. Data shown is based on steady state operating conditions of 77° F, 28.42 in HG and number 2 diesel fuel with 35° API and LHV of 18,390 BTU/lb. The nominal emissions data shown is subject to instrumentation, measurement, facility and engine to engine variations. Emissions data is based on 100% load and thus cannot be used to compare to EPA regulations which use values based on a weighted cycle.
- ³ UL 2200 Listed packages may have oversized generators with a different temperature rise and motor starting characteristics. Generator temperature rise is based on a 40° C ambient per NEMA MG1-32.
- *Governing Class capability as per ISO 8528-5. Consult your local Cat dealer for configuration and site specific transient performance classification.

www.cat.com/electricpower

©2025 Caterpillar All rights reserved.