

Standby & Prime: 60Hz



Image shown might not reflect actual configuration

Engine Model	Cat® C9 ACERT™ In-line 6, 4-cycle diesel
Bore x Stroke	112mm x 149mm (4.4in x 5.9in)
Displacement	8.8 L (538 in³)
Compression Ratio	16.1:1
Aspiration	Turbocharged Air-to-Air Aftercooled
Fuel Injection System	HEUI
Governor	Electronic ADEM™ A4 - G3 Class* capable


Model	Standby	Prime	Emission Strategy
DE200SE0	250 kVA, 200 ekW	225 kVA, 180 ekW	Non-Certified Emissions

PACKAGE PERFORMANCE

Performance	Standby	Prime
Frequency	60 Hz	
Genset Power Rating	250 kVA	225 kVA
Genset power rating with fan @ 0.8 power factor	200 ekW	180 ekW
Emissions	Non-Certified Emissions	
Performance Number	EM0884	EM1041
Fuel Consumption		
100% load with fan, L/hr (gal/hr)	54.4 (14.4)	49.9 (13.1)
75% load with fan, L/hr (gal/hr)	42.3 (11.2)	38.9 (10.3)
50% load with fan, L/hr (gal/hr)	31.4 (8.3)	28.7 (7.6)
25% load with fan, L/hr (gal/hr)	20.4 (5.4)	19.3 (5.1)
Cooling System¹		
Radiator air flow restriction (system), kPa (in. Water)	0.12 (0.48)	0.12 (0.48)
Radiator air flow, m³/min (cfm)	519 (18328)	519 (18328)
Engine coolant capacity, L (gal)	13.9 (3.7)	13.9 (3.7)
Radiator coolant capacity, L (gal)	43 (11.5)	43 (11.5)
Total coolant capacity, L (gal)	56.9 (15.2)	56.9 (15.2)
Inlet Air		
Combustion air inlet flow rate, m³/min (cfm)	18.5 (644)	17.1 (605)
Max. Allowable Combustion Air Inlet Temp, °C (°F)	48 (118)	48 (118)
Exhaust System		
Exhaust stack gas temperature, °C (°F)	411 (771)	402 (756)
Exhaust gas flow rate, m³/min (cfm)	42.7 (1511)	40 (1396)
Exhaust system backpressure (maximum allowable) kPa (in. water)	10.0 (40.0)	10.0 (40.0)
Heat Rejection		
Heat rejection to jacket water, kW (Btu/min)	103 (5888)	97 (5504)
Heat rejection to exhaust (total) kW (Btu/min)	174 (9895)	160 (9084)
Heat rejection to aftercooler, kW (Btu/min)	39 (2227)	34 (1897)
Heat rejection to atmosphere from engine, kW (Btu/min)	24 (1388)	23.1 (1318)

Emissions (Nominal) ²	Standby			Prime	
NOx, mg/Nm³ (g/hp-hr)	4657 (9.8)			4475 (9.4)	
CO, mg/Nm³ (g/hp-hr)	320.2 (0.67)			297 (0.73)	
HC, mg/Nm³ (g/hp-hr)	20.4 (0.05)			21.5 (0.05)	
PM, mg/Nm³ (g/hp-hr)	22.4 (0.06)			26.6 (0.07)	
Alternator ³					
Voltages	220V	240V	380V	440V	480V
Motor starting capability @ 30% Voltage Dip	426 skVA	507 skVA	318 skVA	426 skVA	507 skVA
Current	656 amps	601 amps	380 amps	328 amps	301 amps
Frame Size	R2473L4	R2473L4	R2473L4	R2473L4	R2473L4
Excitation	SE	SE	SE	SE	SE
Temperature Rise	130°C	130°C	130°C	130°C	130°C

WEIGHTS & DIMENSIONS



Note: General configuration not to be used for installation. See general dimension drawings for detail.

Dim "A" mm (in)	Dim "B" mm (in)	Dim "C" mm (in)	Dry Weight kg (lb)
2662 (89)	1030 (41)	1754 (69)	2096 (4621)

APPLICABLE CODES AND STANDARDS:

AS1359, CSA C22.2 No100-04, UL142, UL489, UL869, UL2200, NFPA37, NFPA70, NFPA99, NFPA110, IBC, IEC60034-1, ISO3046, ISO8528, NEMA MG1-22, NEMA MG1-33, 2006/95/EC, 2006/42/EC, 2004/108/EC.

Note: Codes may not be available in all model configurations. Please consult your local Cat Dealer representative for availability.

STANDBY: Output available with varying load for the duration of the interruption of the normal source power. Average power output is 70% of the standby power rating. Typical operation is 200 hours per year, with maximum expected usage of 500 hours per year.

PRIME: Output available with varying load for an unlimited time. Average power output is 70% of the prime power rating. Typical peak demand is 100% of prime rated kW with 10% overload capability for emergency use for a maximum of 1 hour in 12. Overload operation cannot exceed 25 hours per year

RATINGS: Ratings are based on SAE J1349 standard conditions. These ratings also apply at ISO3046 standard conditions.

DEFINITIONS AND CONDITIONS

¹ For ambient and altitude capabilities consult your Cat dealer. Air flow restriction (system) is added to existing restriction from factory.

² Emissions data measurement procedures are consistent with those described in EPA CFR 40 Part 89, Subpart D & E and ISO8178-1 for measuring HC, CO, PM, NOx. Data shown is based on steady state operating conditions of 77° F, 28.42 in HG and number 2 diesel fuel with 35° API and LHV of 18,390 BTU/lb. The nominal emissions data shown is subject to instrumentation, measurement, facility and engine to engine variations. Emissions data is based on 100% load and thus cannot be used to compare to EPA regulations which use values based on a weighted cycle.

³ UL 2200 Listed packages may have oversized generators with a different temperature rise and motor starting characteristics. Generator temperature rise is based on a 40° C ambient per NEMA MG1-32.

* Governing Class capability as per ISO8528-5. Consult your local Cat dealer for configuration and site specific transient performance classification.

LET'S DO THE WORK.™

LEHE1618-03 (10/24)

www.cat.com/electricpower
 © 2024 Caterpillar. All Rights Reserved.
 Materials and specifications are subject to change without notice. The International System of Units (SI) is used in this publication.
 CAT, CATERPILLAR, LET'S DO THE WORK, their respective logos, "Caterpillar Corporate Yellow", the "Power Edge" and Cat "Modern Hex" trade dress as well as corporate and product identity used herein, are trademarks of Caterpillar and may not be used without permission.