# Cat® C18

## **Diesel Generator Sets**



### Standby & Prime: 50 Hz



Engine Model	Cat® C18 In-line 6, 4-cycle Diesel
Bore x Stroke	145 mm x 183 mm (5.7 in x 7.2 in)
Displacement	18.1 L (1106 in³)
Compression Ratio	14.5:1
Aspiration	Turbocharged Air-to-Air Aftercooled
Fuel Injection System	MEUI
Governor	Electronic ADEM™ A4 - G3 Class* capable

Model	Standby	Prime	Emission Strategy
DE605E0	605 kVA, 484 ekW	550 kVA, 440 ekW	Low BSFC

### **PACKAGE PERFORMANCE**

Performance	Standby	Prime	
Frequency	50	50 Hz	
Genset power rating	605 kVA	550 kVA	
Genset power rating with fan @ 0.8 pf	484 ekW	440 ekW	
Emissions	Low	BSFC	
Performance number	DM9820	DM9819	
Fuel Consumption			
100% load with fan, L/hr (gal/hr)	122.7 (32.4)	111 0 (29.3)	
75% load with fan, L/hr (gal/hr)	92.0 (24.3)	83.9 (22.2)	
50% load with fan, L/hr (gal/hr)	64.0 (16 9)	58.8 (15.5)	
25% load with fan , L/hr (gal/hr)	37.2 (9.8)	34.4 (9.1)	
Cooling System <sup>1</sup>			
Radiator air flow restriction (system), kPa (in. water)	0.12 (0.48)	0.12 (0.48)	
Radiator air flow, m³/min (CFM)	373 (13172)	373 (13172)	
Engine coolant capacity, L (gal)	20.8 (5.5)	20.8 (5.5)	
Radiator coolant capacity, L (gal)	34 (8.9)	34 (8.9)	
Total coolant capacity, L (gal)	54.8 (14.4)	54.8 (14.4)	
Inlet Air			
Combustion air inlet flow rate, m³/min (CFM)	31.6 (1117.5)	29.2 (1032.0)	
Max. allowable combustion air inlet temp, °C (°F)	49 (121)	47 (117)	
Exhaust System			
Exhaust stack gas temperature, °C (°F)	553.8 (1028.8)	543.1 (1009.6)	
Exhaust gas flow rate, m³/min (CFM)	92.1 (3251.0)	83.5 (2948.0)	
Exhaust system backpressure (maximum allowable), kPa (in. water)	10.0 (40.0)	10.0 (40.0)	
Exhaust System			
Heat rejection to jacket water, kW (Btu/min)	157 (8945)	146 (8309)	
Heat rejection to exhaust (total), kW (Btu/min)	449 (25525)	404 (22965)	
Heat rejection to aftercooler, kW (Btu/min)	76 (4313)	63 (3606)	
Heat rejection to atmosphere from engine, kW (Btu/min)	84 (4784)	78 (4438)	
Heat rejection to atmosphere from generator, kW (Btu/min)	36 (2047)	31 (1763)	

LEHE1658-03 1/2


# C18 Diesel Generator Sets Electric Power




Emissions (Nominal) <sup>2</sup>				
NOx, mg/Nm³ (g/hp-hr)	3762.8 (7.7)		4029.2 (8.1)	
CO, mg/Nm³ (g/hp-hr)	656.7 (1.3)		615.0 (1.2)	
HC, mg/Nm³ (g/hp-hr)	3.2 (0.0)		3.3 (0.0)	
PM, mg/Nm³ (g/hp-hr)	12.6 (0.0)		10.4 (0.0)	
Alternator <sup>3</sup>				
Voltages	380V	40	0V	415V
Voltages Motor Starting Capability @ 30% Voltage Dip	380V 1362 skVA	_	0V skVA	415V 1539 skVA
		1507		-
Motor Starting Capability @ 30% Voltage Dip	1362 skVA	1507	skVA , PP: 794A	1539 skVA
Motor Starting Capability @ 30% Voltage Dip Current	1362 skVA SB: 919A, PP: 811A	1507 SB: 873A A33	skVA , PP: 794A	1539 skVA SB: 842A, PP: 765A

SB: Standby PP: Prime Power.

### **WEIGHTS & DIMENSIONS**





Dim "A" mm (in)	Dim "B" mm (in)	Dim "C" mm (in)	Dry Weight kg (lb)
3910 (154)	1461 (58)	2156 (85)	3740 (8245)

Note: General configuration not to be used for installation. See general dimension drawings for detail.

### **APPLICABLE CODES AND STANDARDS:**

AS1359, IEC60034-1, ISO3046, ISO8528, NEMA MG1-33, UKCA, CE, EAC. **Note:** Codes may not be available in all model configurations. Please consult your local Cat Dealer representative for availability.

**STANDBY:** Output available with varying load for the duration of the interruption of the normal source power. Average power output is 70% of the standby power rating. Typical operation is 200 hours per year, with maximum expected usage of 500 hours per year.

**PRIME:** Output available with varying load for an unlimited time. Average power output is 70% of the prime power rating. Typical peak demand is 100% of prime rated ekW with 10% overload capability for emergency use for a maximum of 1 hour in 12. Overload operation cannot exceed 25 hours per year

RATINGS: Ratings are based on SAE J1349 standard conditions. These ratings also apply at ISO3046 standard conditions.

#### **DEFINITIONS AND CONDITIONS**

- <sup>1</sup> For ambient and altitude capabilities consult your Cat dealer. Air flow restriction (system) is added to existing restriction from factory.
- <sup>2</sup> Emissions data measurement procedures are consistent with those described in EPA CFR 40 Part 89, Subpart D & E and ISO8178-1 for measuring HC, CO, PM, NOx. Data shown is based on steady state operating conditions of 77° F, 28.42 in HG and number 2 diesel fuel with 35° API and LHV of 18,390 BTU/lb. The nominal emissions data shown is subject to instrumentation, measurement, facility and engine to engine variations. Emissions data is based on 100% load and thus cannot be used to compare to EPA regulations which use values based on a weighted cycle.
- <sup>3</sup> Generator temperature rise is based on a 40° C ambient per IEC60034-1.
- \* Governing Class capability as per ISO8528-5. Consult your local Cat dealer for configuration and site specific transient performance classification.

## **LET'S DO THE WORK.**

www.cat.com/electricpower