

## Standby & Prime: 50Hz



Image shown might not reflect actual configuration

Engine Model	Cat® C13 ACERT™ In-line 6, 4-cycle diesel
Bore x Stroke	130mm x 157mm (5.1 in x 6.2 in)
Displacement	12.5 L (763 in³)
Compression Ratio	16.3:1
Aspiration	Turbocharged Air-to-Air Aftercooled
Fuel Injection System	MEUI
Governor	Electronic ADEM™ A4


Model	Standby	Prime	Emission Strategy
DE350C3	400 kVA	350 kVA, 280 kW	China Non-Road III

## PACKAGE PERFORMANCE

Performance	Standby	Prime
Frequency	50 Hz	
Genset Power Rating	400 kVA	350 kVA
Genset power rating with fan @ 0.8 power factor	NA	280 kW
Emissions	China Non-Road III	
Performance Number	EM1443	EM1458
<b>Fuel Consumption</b>		
100% load with fan, L/hr (gal/hr)	96.9 (25.6)	80.7 (21.3)
75% load with fan, L/hr (gal/hr)	75.8 (20.0)	64.5 (17.0)
50% load with fan, L/hr (gal/hr)	55.5 (14.7)	46.4 (12.2)
25% load with fan, L/hr (gal/hr)	32.4 (8.5)	25.8 (6.8)
<b>Cooling System¹</b>		
Radiator air flow restriction (system), kPa (in. Water)	0.12 (0.48)	0.12 (0.48)
Radiator air flow, m³/min (cfm)	396 (13985)	396 (13985)
Engine coolant capacity, L (gal)	14.2 (3.7)	14.2 (3.7)
Radiator coolant capacity, L (gal)	25 (6.6)	25 (6.6)
Total coolant capacity, L (gal)	39.2 (10.3)	39.2 (10.3)
<b>Inlet Air</b>		
Combustion air inlet flow rate, m³/min (cfm)	26.4 (932.3)	25 (882.8)
Max. Allowable Combustion Air Inlet Temp, °C (°F)	50 (122)	50 (122)
<b>Exhaust System</b>		
Exhaust stack gas temperature, °C (°F)	516 (962)	490 (915)
Exhaust gas flow rate, m³/min (cfm)	74 (2616)	66.8 (2361)
Exhaust system backpressure (maximum allowable) kPa (in. water)	10.0 (40.0)	10.0 (40.0)
<b>Heat Rejection</b>		
Heat rejection to jacket water, kW (Btu/min)	135 (7677)	114 (6483)
Heat rejection to exhaust (total) kW (Btu/min)	333 (18937)	284 (16150)
Heat rejection to aftercooler, kW (Btu/min)	80.2 (4561)	68.5 (3896)
Heat rejection to atmosphere from engine, kW (Btu/min)	75 (4265)	63.1 (3588)

Emissions (Nominal) <sup>2</sup>	Standby	Prime
NOx, mg/Nm <sup>3</sup> (g/hp-hr)	1670 (3.4)	1198 (2.5)
CO, mg/Nm <sup>3</sup> (g/hp-hr)	483 (1.01)	360 (0.83)
HC, mg/Nm <sup>3</sup> (g/hp-hr)	4.4 (0.01)	6.0 (0.02)
Alternator <sup>3</sup>		
Voltages	440V	
Motor starting capability @ 30% Voltage Dip	996 skVA	
Current	505 amps	
Frame Size	A2925L4	
Excitation	SE	
Temperature Rise	125°C	

## WEIGHTS & DIMENSIONS



**Note:** General configuration not to be used for installation. See general dimension drawings for detail.

Dim "A" mm (in)	Dim "B" mm (in)	Dim "C" mm (in)	Dry Weight kg (lb)
3830 (151)	1130 (44)	2156 (85)	3253 (7172)

## APPLICABLE CODES AND STANDARDS:

AS1359, CSA C22.2 No100-04, UL142, UL489, UL869, UL2200, NFPA37, NFPA70, NFPA99, NFPA110, IBC, IEC60034-1, ISO3046, ISO8528, NEMA MG1-22, NEMA MG1-33, 2006/95/EC, 2006/42/EC, 2004/108/EC.

Note: Codes may not be available in all model configurations. Please consult your local Cat Dealer representative for availability.

**STANDBY:** Output available with varying load for the duration of the interruption of the normal source power. Average power output is 70% of the standby power rating. Typical operation is 200 hours per year, with maximum expected usage of 500 hours per year.

**PRIME:** Output available with varying load for an unlimited time. Average power output is 70% of the prime power rating. Typical peak demand is 100% of prime rated kW with 10% overload capability for emergency use for a maximum of 1 hour in 12. Overload operation cannot exceed 25 hours per year.

**RATINGS:** Ratings are based on SAE J1349 standard conditions. These ratings also apply at ISO3046 standard conditions.

## DEFINITIONS AND CONDITIONS

<sup>1</sup> For ambient and altitude capabilities consult your Cat dealer. Air flow restriction (system) is added to existing restriction from factory.

<sup>2</sup> Emissions data measurement procedures are consistent with those described in EPA CFR 40 Part 89, Subpart D & E and ISO8178-1 for measuring HC, CO, PM, NOx. Data shown is based on steady state operating conditions of 77° F, 28.42 in HG and number 2 diesel fuel with 35° API and LHV of 18,390 BTU/lb. The nominal emissions data shown is subject to instrumentation, measurement, facility and engine to engine variations. Emissions data is based on 100% load and thus cannot be used to compare to EPA regulations which use values based on a weighted cycle.

<sup>3</sup> UL 2200 Listed packages may have oversized generators with a different temperature rise and motor starting characteristics. Generator temperature rise is based on a 40° C ambient per NEMA MG1-32.

# LET'S DO THE WORK.™

LEHE1705-01 (05/20)

Materials and specifications are subject to change without notice. The International System of Units (SI) is used in this publication.  
© 2020 Caterpillar. All Rights Reserved. CAT, CATERPILLAR, LET'S DO THE WORK, their respective logos, "Caterpillar Corporate Yellow", the "Power Edge" and Cat "Modern Hex" trade dress as well as corporate and product identity used herein, are trademarks of Caterpillar and may not be used without permission

www.Cat.com/electricpower  
All rights reserved.