

Standby & Prime: 60Hz



Image shown might not reflect actual configuration

Engine Model	Cat® C18 In-line 6, 4-cycle Diesel
Bore x Stroke	145mm x 183mm (5.7in x 7.2in)
Displacement	18.13 L (1106.3 in³)
Compression Ratio	14:1
Aspiration	Turbocharged Air-to-Air Aftercooled
Fuel Injection System	Electronic Unit Injection
Governor	Electronic ADEM™ A4 - G3 Class* capable


Model	Standby	Prime	Emission Strategy
DE650SE0	650 ekW	600 ekW	Low BSFC

PACKAGE PERFORMANCE

Performance	Standby	Prime
Frequency	60 Hz	
Genset power rating	812 kVA	750 kVA
Genset power rating with fan @ 0.8 pf	650 ekW	600 ekW
Emissions	Low BSFC	
Performance number	EM3832	EM3833
Fuel Consumption		
100% load with fan, L/hr (gal/hr)	171.6 (45.3)	158.9 (41.9)
75% load with fan, L/hr (gal/hr)	124.5 (32.8)	114.9 (30.3)
50% load with fan, L/hr (gal/hr)	86.1 (22.7)	80.7 (21.3)
25% load with fan, L/hr (gal/hr)	51.5 (13.6)	48.9 (12.9)
Cooling System¹		
Radiator air flow restriction (system), kPa (in. water)	0.12 (0.48)	0.12 (0.48)
Radiator air flow, m³/min (CFM)	899 (31748)	
Engine coolant capacity, L (gal)	21 (5.5)	21 (5.5)
Radiator coolant capacity, L (gal)	89 (23.5)	89 (23.5)
Total coolant capacity, L (gal)	110 (29.1)	110 (29.1)
Inlet Air		
Combustion air inlet flow rate, m³/min (CFM)	62.8 (2217.2)	60.6 (2139.2)
Max. Allowable Combustion Air Inlet Temp, °C (°F)	49 (120)	
Exhaust System		
Exhaust stack gas temperature, °C (°F)	409.2 (2127)	393.9 (741)
Exhaust gas flow rate, m³/min (CFM)	148.3 (5237)	139.5 (4924.6)
Exhaust system backpressure (maximum allowable), kPa (in. water)	10 (40.1)	
Heat Rejection		
Heat rejection to jacket water, kW (Btu/min)	200 (11351)	187 (10652)
Heat rejection to exhaust (total), kW (Btu/min)	623 (35417)	573 (32608)
Heat rejection to aftercooler, kW (Btu/min)	227 (12893)	211 (11976)
Heat rejection to atmosphere from engine, kW (Btu/min)	92 (5229)	87.6 (4984)

Emissions (Nominal) ²	Standby			Prime		
NOx, mg/Nm³ (g/hp-hr)	2538.9 (5.47)			2394.7 (5.11)		
CO, mg/Nm³ (g/hp-hr)	78.0 (0.17)			64.6 (0.14)		
HC, mg/Nm³ (g/hp-hr)	19.4 (0.05)			28.4 (0.07)		
PM, mg/Nm³ (g/hp-hr)	8.3 (0.02)			9.1 (0.02)		
Alternator ³						
Voltages	480 V	440 V	380 V	480 V	440 V	380 V
Motor starting capability @ 30% Voltage Dip & 0.6 pf	2147 skVA	1829 skVA	1390 skVA	2147 skVA	1829 skVA	1390 skVA
Current	977.3 amps	1066.1 amps	1169.9 amps	902 amps	984 amps	1139.5 amps
Frame Size	LC7224H	LC7224H	LC7224H	LC7224H	LC7224H	LC7224H
Excitation	AREP	AREP	AREP	AREP	AREP	AREP
Temperature Rise	130°C	130°C	130°C	130°C	130°C	130°C

WEIGHTS & DIMENSIONS



Dim "A" mm (in)	Dim "B" mm (in)	Dim "C" mm (in)	Dry Weight kg (lb)
3910 (154)	1461 (58)	2156 (85)	3862 (8514)

APPLICABLE CODES AND STANDARDS:

AS1359, IEC60034-1, ISO3046, ISO8528, NEMA MG1-33, EAC,CE,UKCA.

Note: Codes may not be available in all model configurations. Please consult your local Cat Dealer representative for availability.

STANDBY: Output available with varying load for the duration of the interruption of the normal source power. Average power output is 70% of the standby power rating. Typical operation is 200 hours per year, with maximum expected usage of 500 hours per year.

PRIME: Output available with varying load for an unlimited time. Average power output is 70% of the prime power rating. Typical peak demand is 100% of prime rated kW with 10% overload capability for emergency use for a maximum of 1 hour in 12. Overload operation cannot exceed 25 hours per year.

RATINGS: Ratings are based on SAE J1349 standard conditions. These ratings also apply to ISO3046 standard conditions.

DEFINITIONS AND CONDITIONS

¹ For ambient and altitude capabilities consult your Cat dealer. Air flow restriction (system) is added to existing restriction from factory.

² Emissions data measurement procedures are consistent with those described in EPA CFR 40 Part 89, Subpart D & E and ISO8178-1 for measuring HC, CO, PM, NOx. Data shown is based on steady state operating conditions of 77° F, 28.42 in HG and number 2 diesel fuel with 35° API and LHV of 18,390 BTU/lb. The nominal emissions data shown is subject to instrumentation, measurement, facility and engine to engine variations. Emissions data is based on 100% load and thus cannot be used to compare to EPA regulations which use values based on a weighted cycle.

³ Generator temperature rise is based on a 40° C ambient per IEC60034-1.

* Governing Class capability as per ISO-8528-5. Consult your local Cat dealer for configuration and site specific transient performance classification.

LET'S DO THE WORK.™