

# Cat® C18

## Diesel Generator Sets



### Standby & Prime: 60 Hz



Image shown might not reflect actual configuration.

Engine Model	Cat® C18 In-line 6, 4-cycle Diesel
Bore x Stroke	145 mm x 183 mm (5.7 in x 7.2 in)
Displacement	18.13 L (1106.3 in³)
Compression Ratio	14:1
Aspiration	Turbocharged Air-to-Air Aftercooled
Fuel Injection System	Electronic Unit Injection
Governor	Electronic ADEM™ A4 – G3 Class* capable

Model	Standby	Prime	Emission Strategy
C18	750 ekW, 938 kVA	680 ekW, 850 kVA	EPA TIER II


### PACKAGE PERFORMANCE

Performance	Standby	Prime
Frequency	60 Hz	
Genset Power Rating	938 kVA	850 kVA
Genset power rating with fan @ 0.8 power factor	750 ekW	680 ekW
Emissions	EPA TIER II	
Performance Number	EM3842	EM3843
Fuel Consumption		
100% load with fan, L/hr (gal/hr)	200.8 (53.0)	184.3 (48.4)
75% load with fan, L/hr (gal/hr)	160.6 (42.4)	143.0 (37.7)
50% load with fan, L/hr (gal/hr)	106.5 (28.1)	98.0 (25.8)
25% load with fan, L/hr (gal/hr)	62.1 (16.4)	58.0 (15.3)
Cooling System¹		
Radiator air flow restriction (system), kPa (in. water)	0.12 (0.48)	0.12 (0.48)
Radiator air flow, m³/min (CFM)	900 (31783)	900 (31783)
Engine coolant capacity, L (gal)	20.8 (5.5)	20.8 (5.5)
Radiator coolant capacity, L (gal)	77 (20.3)	77 (20.3)
Total coolant capacity, L (gal)	97.8 (25.8)	97.8 (25.8)
Inlet Air		
Combustion air inlet flow rate, m³/min (CFM)	67.3 (2376)	65.6 (2316)
Max. Allowable Combustion Air Inlet Temp, °C (°F)	49 (120)	49 (120)
Exhaust System		
Exhaust stack gas temperature, °C (°F)	452.9 (847.2)	432.9 (811.2)
Exhaust gas flow rate, m³/min (CFM)	170.7 (6028)	161 (5686)
Exhaust system backpressure (maximum allowable), kPa (in. water)	10.0 (40.0)	10.0 (40.0)
Heat Rejection		
Heat rejection to jacket water, kW (BTU/min)	225 (12795)	208 (11828)
Heat rejection to exhaust (total), kW (BTU/min)	714 (40604)	664 (37761)
Heat rejection to aftercooler, kW (BTU/min)	272 (15468)	253 (14387)
Heat rejection to atmosphere from engine, kW (BTU/min)	142 (8075)	123 (6995)

Emissions (Nominal) <sup>2</sup>	Standby	Prime
NOx, mg/Nm <sup>3</sup> (g/hp-hr)	2468 (5.42)	2213 (4.91)
CO, mg/Nm <sup>3</sup> (g/hp-hr)	100.1 (0.22)	75.6 (0.17)
HC, mg/Nm <sup>3</sup> (g/hp-hr)	23.5 (0.06)	24.1 (0.06)
PM, mg/Nm <sup>3</sup> (g/hp-hr)	11.7 (0.03)	10.6 (0.03)

Alternator <sup>3</sup>											
Duty Cycle		Standby					Prime				
Phase		3-Phase					3-Phase				
Voltages, V		208	220	240	480	600	208	220	240	480	600
Current, Amps		2602	2460	2255	1128	902	2359	2231	2045	1022	818
Frame: LC7224J Excitation: AREP	Temperature Rise @ 40°C			150	150	150			125	125	125
	Motor Starting Capability @ 30% Voltage Dip, skVA			2512	2512	2512			2512	2512	2512
Frame: LC7224L Excitation: AREP	Temperature Rise @ 40°C	150	130	105	105	130	125	105	105	105	105
	Motor Starting Capability @ 30% Voltage Dip, skVA	1917	2129	2501	2501	2503	1917	2129	2501	2501	2503
Frame: LC7224N Excitation: AREP	Temperature Rise @ 40°C	130	105			105	105	105			80
	Motor Starting Capability @ 30% Voltage Dip, skVA	2403	2666			3368	2403	2666			3368
Frame: LC7224P Excitation: AREP	Temperature Rise @ 40°C	105		80	80		80		80	80	
	Motor Starting Capability @ 30% Voltage Dip, skVA	2392		3120	3120		2392		3120	3120	

WEIGHTS & DIMENSIONS



Dim "A" mm (in)	Dim "B" mm (in)	Dim "C" mm (in)	Dry Weight kg (lb)
3512 (138)	1746 (69)	2322 (92)	4863 (10721)

**Note:** General configuration not to be used for installation. See general dimension drawings for detail.

APPLICABLE CODES AND STANDARDS:

CSA C22.2 No 100-04, UL489, UL869, UL2200, IBC, IEC60034-1, ISO 3046, ISO 8528, NEMA MG 1-22, NEMA MG 1-33 and facilitates the compliance to NFPA 37, NFPA70, NFPA 99, NFPA110.

**Note:** Codes may not be available for all model configurations. Site level review needed for NFPA 70. Please consult your Cat Dealer for availability.

**STANDBY:** Output available with varying load for the duration of the interruption of the normal source power. Average power output is 70% of the standby power rating. Typical operation is 200 hours per year, with maximum expected usage of 500 hours per year.

**PRIME:** Output available with varying load for an unlimited time. Average power output is 70% of the prime power rating. Typical peak demand is 100% of prime rated kW with 10% overload capability for emergency use for a maximum of 1 hour in 12. Overload operation cannot exceed 25 hours per year.

**RATINGS:** Ratings are based on SAE J1349 standard conditions. These ratings also apply at ISO 3046 standard conditions.

DEFINITIONS AND CONDITIONS

<sup>1</sup> For ambient and altitude capabilities consult your Cat dealer. Air flow restriction (system) is added to existing restriction from factory.

<sup>2</sup> Emissions data measurement procedures are consistent with those described in EPA CFR 40 Part 89, Subpart D & E and ISO8178-1 for measuring HC, CO, PM, NOx. Data shown is based on steady state operating conditions of 77° F, 28.42 in HG and number 2 diesel fuel with 35° API and LHV of 18,390 BTU/lb. The nominal emissions data shown is subject to instrumentation, measurement, facility and engine to engine variations. Emissions data is based on 100% load and thus cannot be used to compare to EPA regulations which use values based on a weighted cycle.

<sup>3</sup> UL 2200 Listed packages may have oversized generators with a different temperature rise and motor starting characteristics. Generator temperature rise is based on a 40° C ambient per NEMA MG1-32.

\*Governing Class capability as per ISO 8528-5. Consult your local Cat dealer for configuration and site specific transient performance classification.