

Cat® C175-20

Diesel Generator Sets



Image shown may not reflect actual configuration

Bore – mm (in)	175 (6.89)
Stroke – mm (in)	220 (8.66)
Displacement – L (in ³)	105.8 (6456)
Compression Ratio	15.3:1
Aspiration	TA
Fuel System	Common Rail
Governor Type	ADEM™ A4

Standby 50 Hz kVA (ekW)	Mission Critical 50 Hz kVA (ekW)	Emissions Performance
3350 (3183)	3350 (3183)	Optimized for Low Emissions

Features

Cat® Diesel Engine

- Designed and optimized for low emissions
- Reliable performance proven in thousands of applications worldwide
- Certified alternative fuels including Hydrotreated Vegetable Oil (HVO), Renewable Diesel (RD) and Hydrotreated Renewable Diesel (HRD) which meet EN 15940 or ASTM D975 can be used or blended with EN 590 diesel

Generator Set Package

- Accepts 100% block load in one step
- Meets NFPA 110 loading requirements
- Conforms to ISO 8528-5 G3 load acceptance requirements
- Reliability verified through torsional vibration, fuel consumption, oil consumption, transient performance, and endurance testing

Alternators

- Superior motor starting capability minimizes need for oversizing generator
- Designed to match performance and output characteristics of Cat diesel engines

Cat Energy Control System (ECS)

- User-friendly interface and navigation
- Scalable system to meet a wide range of installation requirements
- Expansion modules and site specific programming for specific customer requirements
- Graphical touchscreen display
- Easily upgradeable

Warranty

- 24 months/1000-hour warranty for standby and mission critical ratings
- Extended service protection is available to provide extended coverage options

Worldwide Product Support

- Cat dealers have over 1,800 dealer branch stores operating in 200 countries
- Your local Cat dealer provides extensive post-sale support, including maintenance and repair agreements

Financing

- Caterpillar offers an array of financial products to help you succeed through financial service excellence
- Options include loans, finance lease, operating lease, working capital, and revolving line of credit
- Contact your local Cat dealer for availability in your region

Standard and Optional Equipment

Engine

Air Cleaner

- Single element

Muffler

- Industrial grade (15 dB)
- Residential grade (25 dB)
- Critical grade (35 dB)

Starting

- Standard batteries
- Oversized batteries
- Standard electric starter(s)
- Heavy duty electric starter(s)
- Dual electric starter(s)
- Air starter(s)
- Jacket water heater

Alternator

Output voltage

- 400V
- 415V

Temperature Rise (over 40°C ambient)

- 150°C

Winding type

- Random wound

Excitation

- Permanent magnet (PM)

Attachments

- Anti-condensation heater
- Stator and bearing temperature monitoring and protection

Control System

Controller

- Cat ECS 100
- Cat ECS 200

Attachments

- Local annunciator module
- Remote annunciator module
- Expansion I/O module
- Remote monitoring software

Charging

- Battery charger – 20A
- Battery charger – 35A
- Battery charger – 50A

Vibration Isolators

- Rubber
- Spring
- Seismic rated

Cat Connect

Connectivity

- Ethernet
- Cellular

Extended Service Options

Terms

- 2 year (prime)
- 3 year
- 5 year
- 10 year

Coverage

- Silver
- Gold
- Platinum
- Platinum Plus

Ancillary Equipment

- Automatic transfer switch (ATS)
- Paralleling switchgear
- Paralleling controls

Certifications

- EU & GB Declaration of Incorporation

Note: Some options may not be available on all models. Certifications may not be available with all model configurations. Consult factory for availability.


Package Performance

Low Emissions

Performance	Standby	Mission Critical
Frequency	50 Hz	50 Hz
Gen set power rating without fan	3183 ekW	3183 ekW
Gen set power rating without fan @ 0.8 power factor	3350 kVA	3350 kVA
Emissions	Low Emissions	Low Emissions
Performance number	EM7552-00	EM7509-00
Fuel Consumption		
100% load without fan – L/hr (gal/hr)	792.0 (209.2)	792.0 (209.2)
75% load without fan – L/hr (gal/hr)	629.8 (166.4)	629.8 (166.4)
50% load without fan – L/hr (gal/hr)	423.0 (111.8)	423.0 (111.8)
25% load without fan – L/hr (gal/hr)	235.8 (62.3)	235.8 (62.3)
Cooling System		
Engine coolant capacity – L (gal)	440.0 (116.2)	440.0 (116.2)
Inlet Air		
Combustion air inlet flow rate – m ³ /min (cfm)	304.7 (10757.5)	304.7 (10757.5)
Exhaust System		
Exhaust stack gas temperature – °C (°F)	458.3 (857.0)	458.3 (857.0)
Exhaust gas flow rate – m ³ /min (cfm)	700.1 (24720.1)	700.1 (24720.1)
Exhaust system backpressure (maximum allowable) – kPa (in. water)	6.7 (27.0)	6.7 (27.0)
Heat Rejection		
Heat rejection to jacket water – kW (Btu/min)	1720 (97805)	1720 (97805)
Heat rejection to exhaust (total) – kW (Btu/min)	2995 (170345)	2995 (170345)
Heat rejection to aftercooler – kW (Btu/min)	368 (20907)	368 (20907)
Heat rejection to atmosphere from engine – kW (Btu/min)	195 (11084)	195 (11084)
Heat rejection from alternator – kW (Btu/min)	140 (7969)	140 (7969)
Emissions* (Nominal)		
NO _x mg/Nm ³ (g/hp-h)	2274.9 (4.88)	2274.9 (4.88)
CO mg/Nm ³ (g/hp-h)	272.0 (0.58)	272.0 (0.58)
HC mg/Nm ³ (g/hp-h)	43.4 (0.11)	43.4 (0.11)
PM mg/Nm ³ (g/hp-h)	5.1 (0.01)	5.1 (0.01)
Emissions* (Potential Site Variation)		
NO _x mg/Nm ³ (g/hp-h)	2729.8 (5.85)	2729.8 (5.85)
CO mg/Nm ³ (g/hp-h)	489.7 (1.04)	489.7 (1.04)
HC mg/Nm ³ (g/hp-h)	57.7 (0.14)	57.7 (0.14)
PM mg/Nm ³ (g/hp-h)	7.1 (0.02)	7.1 (0.02)

*mg/Nm³ levels are corrected to 5% O₂. Contact your local Cat dealer for further information.

Weights and Dimensions



Dim "A" mm (in)	Dim "B" mm (in)	Dim "C" mm (in)	Dry Weight kg (lb)
6975 (274.6)	2076 (81.7)	2221 (87.5)	23 420 (51,632)

Note: For reference only. Do not use for installation design. Contact your local Cat dealer for precise weights and dimensions.

Ratings Definitions

Standby

Output available with varying load for the duration of the interruption of the normal source power. Average power output is 70% of the standby rated kW. Typical operation is 200 hours per year, with maximum expected usage of 500 hours per year.

Mission Critical

Output available with varying load for the duration of the interruption of the normal source power. Average power output is 85% of the mission critical rated kW. Typical peak demand up to 100% of rated kW for up to 5% of the operating time. Typical operation is 200 hours per year, with maximum expected usage of 500 hours per year.

Applicable Codes and Standards

AS 1359, IBC, IEC 60034-1, ISO 3046, ISO 8528, NEMA MG1-22, NEMA MG1-33, 2014/35/EU, 2006/42/EC, 2014/30/EU and facilitates compliance to NFPA 37, NFPA 70, NFPA 99, NFPA 110.

Note: Codes may not be available in all model configurations. Please consult your local Cat dealer for availability.

Data Center Applications

- All ratings Tier III/Tier IV compliant per Uptime Institute requirements.
- All ratings ANSI/TIA-942 compliant for Rated-1 through Rated-4 data centers.

Fuel Rates

Fuel consumption reported in accordance with ISO 3046-1, based on fuel oil of 35° API [16°C (60°F)] gravity having an LHV of 42,780 kJ/kg (18,390 Btu/lb) when used at 15°C (59°F) and weighing 850 g/liter (7.0936 lbs/U.S. gal.) All fuel consumption values refer to rated engine power.

www.cat.com/electricpower

©2025 Caterpillar

All rights reserved.

Materials and specifications are subject to change without notice. The International System of Units (SI) is used in this publication.

CAT, CATERPILLAR, LET'S DO THE WORK, their respective logos, "Caterpillar Corporate Yellow", the "Power Edge" and Cat "Modern Hex" trade dress as well as corporate and product identity used herein, are trademarks of Caterpillar and may not be used without permission.