

Cat® C3.3

Diesel Generator Sets



Standby & Prime: 50 Hz & 60 Hz



Image shown might not reflect actual configuration.

Engine Model	Cat® C3.3 Inline 4-stroke Diesel
Bore x Stroke	105.0 mm x 127.0 mm (4.1 in x 5.0 in)
Displacement	3.3 L (201.4 in ³)
Compression Ratio	17.25:1
Aspiration	Turbocharged
Fuel Injection System	Inline
Governor	Mechanical


Model	Standby		Prime		Emission Strategy
DE50EOS	50 Hz		50 Hz		Low BSFC
	50.0 kVA (50.0 kW)		60.0 kVA (60.0 kW)		

PACKAGE PERFORMANCE

Performance		Standby		Prime	
Frequency		50 Hz	60 Hz	50 Hz	60 Hz
Genset Power Rating		50.0 kVA	60.0 kVA	45.0 kVA	55.0 kVA
Genset power rating with fan @ 1.0 power factor		50.0 kW	60.0 kW	45.0 kW	55.0 kW
Emissions		Low BSFC			
Performance Number		P2506B	P2506A	P2506B	P2506A
Fuel Consumption					
Fuel Tank Capacity, litres (US gal)		219 (57.9)			
100% load with fan, L/hr (gal/hr)		14.2 (3.8)	17.3 (4.6)	12.6 (3.3)	15.8 (4.2)
75% load with fan, L/hr (gal/hr)		10.6 (2.8)	13.0 (3.4)	9.6 (2.5)	12.0 (3.2)
50% load with fan, L/hr (gal/hr)		7.4 (2.0)	9.1 (2.4)	6.8 (1.8)	8.5 (2.2)
Cooling System ¹					
Radiator air flow, m ³ /min (CFM)		110.4 (3899)	145.8 (5149)	110.4 (3899)	145.8 (5149)
Total coolant capacity, L (gal)		10.2 (2.7)			
Inlet Air					
Max. Combustion Air Intake Restriction, kPa (in water)		8.0 (32.1)			
Combustion air inlet flow rate, m ³ /min (CFM)		3.9 (138)	4.9 (173)	3.8 (134)	4.7 (166)
Max. Allowable Combustion Air Inlet Temp, °C (°F)		50 (122)			
Exhaust System					
Exhaust stack gas temperature, °C (°F)		571 (1060)	564 (1047)	557 (1035)	534 (993)
Exhaust gas flow rate, m ³ /min (CFM)		10.4 (367)	12.5 (441)	10.1 (357)	11.8 (417)
Exhaust system backpressure (maximum allowable), kPa (in water)		10.0 (3.0)	15.0 (4.4)	10.0 (3.0)	15.0 (4.4)
Heat Rejection					
Heat rejection to jacket water, kW (BTU/min)		37.7 (2144)	42.8 (2434)	35.2 (2002)	41.0 (2332)
Heat rejection to alternator, kW (BTU/min)		5.1 (290)	6.4 (364)	5.1 (290)	6.4 (364)
Heat rejection to atmosphere from engine, kW (BTU/min)		16.1 (916)	17.4 (990)	14.5 (825)	16.7 (950)

Alternator ³	50 Hz		60 Hz	
Voltages	240V	230V	220V	220V
Motor starting capability @ 30% Voltage Dip, skVA	145	136	128	73
Current, amps	208	217	227	250
Temperature Rise, °C			105/40	
Frame Size			M2235L4	
Excitation			S.E	

WEIGHTS & DIMENSIONS



Dim "A" mm (in)	Dim "B" mm (in)	Dim "C" mm (in)	Dry Weight kg (lb)
1925 (75.8)	1120 (44.1)	1361 (53.6)	982 (2164)

Note: General configuration not to be used for installation. See general dimension drawings for detail.

APPLICABLE CODES AND STANDARDS:

AS1359, NFPA37, NFPA70, NFPA99, NFPA110, IBC, IEC60034-1, ISO 3046, IS 8528, NEMA MG1-22, NEMA MG1-33, 2006/95/EC, 2006/42/EC, 2004/108/EC.

Note: Codes may not be available in all model configurations. Please consult your local Cat Dealer representative for availability.

STANDBY: Output available with varying load for the duration of the interruption of the normal source power. Average power output is 70% of the standby power rating. Typical operation is 200 hours per year, with maximum expected usage of 500 hours per year.

PRIME: Output available with varying load for an unlimited time. Average power output is 70% of the prime power rating. Typical peak demand is 100% of prime rated ekW with 10% overload capability for emergency use for a maximum of 1 hour in 12. Overload operation cannot exceed 25 hours per year.

RATINGS: Ratings are based on SAE J1349 standard conditions. These ratings also apply at ISO 3046 standard conditions.

DEFINITIONS AND CONDITIONS

¹ For ambient and altitude capabilities consult your Cat dealer. Air flow restriction (system) is added to existing restriction from factory.

² Emissions data measurement procedures are consistent with those described in EPA CFR 40 Part 89, Subpart D & E and ISO 8178-1 for measuring HC, CO, PM, NOx. Data shown is based on steady state operating conditions of 77°F, 28.42 in HG and number 2 diesel fuel with 35° API and LHV of 18,390 BTU/lb. The nominal emissions data shown is subject to instrumentation, measurement, facility and engine to engine variations. Emissions data is based on 100% load and thus cannot be used to compare to EPA regulations which use values based on a weighted cycle.

³ Generator temperature rise is based on a 40°C ambient per NEMA MG1-32.