

Cat® C175-16

Diesel Generator Sets



Image shown may not reflect actual configuration

Bore – mm (in)	175 (6.89)
Stroke – mm (in)	220 (8.66)
Displacement – L (in ³)	84.7 (5167)
Compression Ratio	16.7:1
Aspiration	TA
Fuel System	Common Rail
Governor Type	ADEM™ A4

Standby 60 Hz ekW (kVA)	Mission Critical 60 Hz ekW (kVA)	Emissions Performance
3100 (3875)	3100 (3875)	U.S. EPA Certified for Emergency Stationary Applications (Tier 2) and meets Northern Virginia NO _x requirements

Features

Cat® Diesel Engine

- Meets U.S. EPA Stationary Emergency (Tier 2) and Northern Virginia NO_x requirements
- Reliable performance proven in thousands of applications worldwide
- Certified alternative fuels including Hydrotreated Vegetable Oil (HVO), Renewable Diesel (RD) and Hydrotreated Renewable Diesel (HRD) which meet EN 15940 or ASTM D975 can be used or blended with EN 590 diesel

Generator Set Package

- Accepts 100% block load in one step
- Meets NFPA 110 loading requirements
- Conforms to ISO 8528-5 G3 load acceptance requirements
- Reliability verified through torsional vibration, fuel consumption, oil consumption, transient performance, and endurance testing

Alternators

- Superior motor starting capability minimizes need for oversizing generator
- Designed to match performance and output characteristics of Cat diesel engines

Cat Energy Control System (ECS)

- User-friendly interface and navigation
- Scalable system to meet a wide range of installation requirements
- Expansion modules and site specific programming for specific customer requirements
- Graphical touchscreen display
- Easily upgradeable

Warranty

- 24 months/1000-hour warranty for standby and mission critical ratings
- Extended service protection is available to provide extended coverage options

Worldwide Product Support

- Cat dealers have over 1,800 dealer branch stores operating in 200 countries
- Your local Cat dealer provides extensive post-sale support, including maintenance and repair agreements

Financing

- Caterpillar offers an array of financial products to help you succeed through financial service excellence
- Options include loans, finance lease, operating lease, working capital, and revolving line of credit
- Contact your local Cat dealer for availability in your region

Standard and Optional Equipment

Engine	Power Termination	Vibration Isolators
Air Cleaner	Type	
<input type="checkbox"/> Single element	<input type="checkbox"/> Bus bar	<input type="checkbox"/> Rubber
<input type="checkbox"/> Dual element	<input type="checkbox"/> Circuit breaker	<input type="checkbox"/> Spring
Muffler	<input type="checkbox"/> 4000A <input type="checkbox"/> 5000A	<input type="checkbox"/> Seismic rated
<input type="checkbox"/> Industrial grade (15 dB)	<input type="checkbox"/> UL <input type="checkbox"/> IEC	
<input type="checkbox"/> Residential grade (25 dB)	<input type="checkbox"/> 3-pole	
<input type="checkbox"/> Critical grade (34 dB)	<input type="checkbox"/> Electrically operated	
Starting	Trip Unit	Cat Connect
<input type="checkbox"/> Standard batteries	<input type="checkbox"/> LSI <input type="checkbox"/> LSI-G	Connectivity
<input type="checkbox"/> Oversized batteries	<input type="checkbox"/> LSIG-P	<input type="checkbox"/> Ethernet
<input type="checkbox"/> Standard electric starter(s)	Control System	<input type="checkbox"/> Cellular
<input type="checkbox"/> Dual electric starter(s)	Controller	
<input type="checkbox"/> Air starter(s)	<input type="checkbox"/> Cat ECS 100	Terms
<input type="checkbox"/> Jacket water heater	<input type="checkbox"/> Cat ECS 200	<input type="checkbox"/> 3 year
Alternator	<input type="checkbox"/> EMCP 4.4	<input type="checkbox"/> 5 year
Output voltage	Attachments	<input type="checkbox"/> 10 year
<input type="checkbox"/> 480V <input type="checkbox"/> 6900V	<input type="checkbox"/> Local annunciator module	Coverage
<input type="checkbox"/> 600V <input type="checkbox"/> 12470V	<input type="checkbox"/> Remote annunciator module	<input type="checkbox"/> Silver
<input type="checkbox"/> 4160V <input type="checkbox"/> 13200V	<input type="checkbox"/> Expansion I/O module	<input type="checkbox"/> Gold
<input type="checkbox"/> 6300V <input type="checkbox"/> 13800V	<input type="checkbox"/> Remote monitoring software	<input type="checkbox"/> Platinum
<input type="checkbox"/> 6600V	Charging	<input type="checkbox"/> Platinum Plus
Temperature Rise <i>(over 40°C ambient)</i>	<input type="checkbox"/> Battery charger – 20A	Ancillary Equipment
<input type="checkbox"/> 150°C	<input type="checkbox"/> Battery charger – 40A	<input type="checkbox"/> Automatic transfer switch (ATS)
<input type="checkbox"/> 125°C/130°C	<input type="checkbox"/> Battery charger – 50A	<input type="checkbox"/> Parallelizing switchgear
<input type="checkbox"/> 105°C		<input type="checkbox"/> Parallelizing controls
<input type="checkbox"/> 80°C		
Winding type		Certifications
<input type="checkbox"/> Form wound		<input type="checkbox"/> UL 2200 Listed
Excitation		<input type="checkbox"/> IBC seismic certification
<input type="checkbox"/> Permanent magnet (PM)		<input type="checkbox"/> OSHPD pre-approval
Attachments		
<input type="checkbox"/> Anti-condensation heater		
<input type="checkbox"/> Stator and bearing temperature monitoring and protection		


Note: Some options may not be available on all models. Certifications may not be available with all model configurations. Consult factory for availability.

Package Performance

Performance	Standby	Mission Critical
Frequency	60 Hz	60 Hz
Gen set power rating without fan	3100 ekW	3100 ekW
Gen set power rating without fan @ 0.8 power factor	3875 kVA	3875 kVA
Emissions	EPA ESE (Tier 2)	EPA ESE (Tier 2)
Performance number	EM6253-01	EM6254-01
Fuel Consumption		
100% load without fan – L/hr (gal/hr)	789.6 (208.6)	789.6 (208.6)
75% load without fan – L/hr (gal/hr)	589.2 (155.7)	589.2 (155.7)
50% load without fan – L/hr (gal/hr)	461.1 (121.8)	461.1 (121.8)
25% load without fan – L/hr (gal/hr)	265.0 (70.0)	265.0 (70.0)
Cooling System		
Engine coolant capacity – L (gal)	377.0 (99.6)	377.0 (99.6)
Inlet Air		
Combustion air inlet flow rate – m ³ /min (cfm)	275.4 (9723.4)	275.4 (9723.4)
Exhaust System		
Exhaust stack gas temperature – °C (°F)	473.3 (883.9)	473.3 (883.9)
Exhaust gas flow rate – m ³ /min (cfm)	708.6 (25020.7)	708.6 (25020.7)
Exhaust system backpressure (maximum allowable) – kPa (in. water)	6.7 (27.0)	6.7 (27.0)
Heat Rejection		
Heat rejection to jacket water – kW (Btu/min)	1409 (80118)	1409 (80118)
Heat rejection to exhaust (total) – kW (Btu/min)	3195 (181715)	3195 (181715)
Heat rejection to aftercooler – kW (Btu/min)	538 (30595)	538 (30595)
Heat rejection to atmosphere from engine – kW (Btu/min)	156 (8885)	156 (8885)
Heat rejection from alternator – kW (Btu/min)	119 (6773)	119 (6773)
Emissions* (Nominal)		
NO _x mg/Nm ³ (g/hp-h)	2568.0 (5.19)	2568.0 (5.19)
CO mg/Nm ³ (g/hp-h)	89.2 (0.21)	89.2 (0.21)
HC mg/Nm ³ (g/hp-h)	14.0 (0.04)	14.0 (0.04)
PM mg/Nm ³ (g/hp-h)	30.8 (0.08)	30.8 (0.08)
Emissions* (Potential Site Variation)		
NO _x mg/Nm ³ (g/hp-h)	3081.6 (6.23)	3081.6 (6.23)
CO mg/Nm ³ (g/hp-h)	160.5 (0.38)	160.5 (0.38)
HC mg/Nm ³ (g/hp-h)	18.6 (0.05)	18.6 (0.05)
PM mg/Nm ³ (g/hp-h)	43.1 (0.12)	43.1 (0.12)

*mg/Nm³ levels are corrected to 5% O₂. Contact your local Cat dealer for further information.

Weights and Dimensions



Dim "A" mm (in)	Dim "B" mm (in)	Dim "C" mm (in)	Dry Weight kg (lb)
6372 (250.9)	2101 (82.7)	2208 (86.9)	19 391 (42,750)

Note: For reference only. Do not use for installation design. Contact your local Cat dealer for precise weights and dimensions.

Ratings Definitions

Standby

Output available with varying load for the duration of the interruption of the normal source power. Average power output is 70% of the standby rated ekW. Typical operation is 200 hours per year, with maximum expected usage of 500 hours per year.

Mission Critical

Output available with varying load for the duration of the interruption of the normal source power. Average power output is 85% of the mission critical rated ekW. Typical peak demand up to 100% of rated ekW for up to 5% of the operating time. Typical operation is 200 hours per year, with maximum expected usage of 500 hours per year.

Applicable Codes and Standards

AS 1359, UL 2200 3rd edition, UL 489, UL 869A, IBC, IEC 60034-1, ISO 3046, ISO 8528, NEMA MG1-22, NEMA MG1-33, 2014/35/EU, 2006/42/EC, 2014/30/EU and facilitates compliance to NFPA 37, NFPA 70, NFPA 99, NFPA 110.

Note: Codes may not be available in all model configurations. Please consult your local Cat dealer for availability.

Data Center Applications

- All ratings Tier III/Tier IV compliant per Uptime Institute requirements.
- All ratings ANSI/TIA-942 compliant for Rated-1 through Rated-4 data centers.

Fuel Rates

Fuel consumption reported in accordance with ISO 3046-1, based on fuel oil of 35° API [16°C (60°F)] gravity having an LHV of 42,780 kJ/kg (18,390 Btu/lb) when used at 15°C (59°F) and weighing 850 g/liter (7.0936 lbs/U.S. gal.) All fuel consumption values refer to rated engine power.