Cat® C7.1 Diesel Generator Sets



Standby & Prime: 50 Hz & 60 Hz



Image shown might not reflect actual configuration.

Engine Model	Cat® C7.1 Inline 4-stroke Diesel
Bore x Stroke	105.0 mm x 135.0 mm (4.1 in x 5.3 in)
Displacement	7.0 L (427.8 in³)
Compression Ratio	16.0:1
Aspiration	Turbocharged Air To Air Charge Cooled
Fuel Injection System	Inline
Governor	Mechanical

Model	Star	ndby	Pri	Emission Strategy	
	50 Hz	60 Hz	50 Hz	60 Hz	
DE165E0	165.0 kVA	187.5 kVA	150.0 kVA	168.8 kVA	Low BSFC
	(132.0 kW)	(150.0 kW)	(120.0 kW)	(135.0 kW)	

PACKAGE PERFORMANCE


Performance	Star	ndby	Pri	Prime		
Frequency	50 Hz	60 Hz	50 Hz	60 Hz		
Genset Power Rating	165.0 kVA	187.5 kVA	150.0 kVA	168.8 kVA		
Genset power rating with fan @ 0.8 power factor	132.0 kW	150.0 kW	120.0 kW	135.0 kW		
Emissions	Low BSFC					
Performance Number	P4200A	P4202A	P4200A	P4202A		
Fuel Consumption						
Fuel Tank Capacity, litres (US gal)	349 (92.2)					
100% load with fan, L/hr (gal/hr)	35.1 (9.3)	41.1 (10.9)	32.4 (8.6)	37.5 (9.9)		
75% load with fan, L/hr (gal/hr)	27.2 (7.2)	31.9 (8.4)	24.9 (6.6)	28.9 (7.6)		
50% load with fan, L/hr (gal/hr)	18.3 (4.8)	21.8 (5.8)	16.6 (4.4)	19.7 (5.2)		
Cooling System ¹						
Radiator air flow, m³/min (cfm)	259.2 (9154)	316.2 (11167)	259.2 (9154)	316.2 (11167)		
Total coolant capacity, L (gal)		21.0	(5.5)			
Inlet Air						
Max. Combustion Air Intake Restriction, kPa (in H₂O)		3.0 (12.0)			
Combustion air inlet flow rate, m³/min (cfm)	10.7 (377)	15.0 (529)	10.0 (354)	14.4 (509)		
Max. Allowable Combustion Air Inlet Temp, °C (°F)	50 (122)					
Exhaust System						
Exhaust stack gas temperature, °C (°F)	484 (903)	407 (765)	484 (903)	407 (765)		
Exhaust gas flow rate, m³/min (cfm)	25.5 (902)	32.2 (1137)	23.9 (843)	31.9 (1125)		
Exhaust system backpressure (maximum allowable), kPa (in H_2O)	6.0 (1.8)	15.0 (4.4)	18.0 (5.3)	15.0 (4.4)		
Heat Rejection						
Heat rejection to jacket water, kW (Btu/min)	75.7 (4305)	80.1 (4555)	69.1 (3930)	73.5 (4180)		
Heat rejection to alternator, kW (Btu/min)	10.2 (580)	11.1 (631)	10.2 (580)	11.1 (631)		
Heat rejection to atmosphere from engine, kW (Btu/min)	22.4 (1274)	23.4 (1331)	19.9 (1132)	20.8 (1183)		

LEHE0709-05 Page 1 of 2



Alternator ³	50 Hz 60 Hz							
Voltages	415V	400V	380V	220V	480V	380V	240V	440V
Motor starting capability @ 30% Voltage Dip, skVA	414	390	358	455	452	307	358	393
Current, amps	230	238	251	375	226	267	451	246
Temperature Rise, °C	163/27	163/27	163/27	163/27	125/40	163/27	125/40	163/27
Frame Size	LC3114J							
Excitation	S.E							

WEIGHTS & DIMENSIONS



2500 (98.4) 1120 (44.1) 1528 (60.2) 1610 (3549)

Note: General configuration not to be used for installation. See general dimension drawings for detail.

APPLICABLE CODES AND STANDARDS:

AS1359, NFPA37, NFPA70, NFPA99, NFPA110, IBC, IEC60034-1, ISO3046, ISO8528, NEMA MG1-22, NEMA MG1-33, 2006/95/EC, 2006/42/EC, 2004/108/EC.

Note: Codes may not be available in all model configurations. Please consult your local Cat Dealer representative for availability.

STANDBY: Output available with varying load for the duration of the interruption of the normal source power. Average power output is 70% of the standby power rating. Typical operation is 200 hours per year, with maximum expected usage of 500 hours per year.

PRIME: Output available with varying load for an unlimited time. Average power output is 70% of the prime power rating. Typical peak demand is 100% of prime rated ekW with 10% overload capability for emergency use for a maximum of 1 hour in 12. Overload operation cannot exceed 25 hours per year

RATINGS: Ratings are based on SAE J1349 standard conditions. These ratings also apply at ISO3046 standard conditions.

DEFINITIONS AND CONDITIONS

- ¹ For ambient and altitude capabilities consult your Cat dealer. Air flow restriction (system) is added to existing restriction from factory.
- ² Emissions data measurement procedures are consistent with those described in EPA CFR 40 Part 89, Subpart D & E and ISO8178-1 for measuring HC, CO, PM, NOx. Data shown is based on steady state operating conditions of 77°F, 28.42 in HG and number 2 diesel fuel with 35° API and LHV of 18,390 BTU/lb. The nominal emissions data shown is subject to instrumentation, measurement, facility and engine to engine variations. Emissions data is based on 100% load and thus cannot be used to compare to EPA regulations which use values based on a weighted cycle.
- ³ Generator temperature rise is based on a 40° C ambient per NEMA MG1-32

www.cat.com/electricpower

©2022 Caterpillar All rights reserved.