## Cat<sup>®</sup> C18 Diesel Generator Sets



Standby & Prime: 50 Hz



Engine Model	Cat <sup>®</sup> C18 In-line 6, 4-cycle diesel
Bore x Stroke	145 mm x 183 mm (5.7 in x 7.2 in)
Displacement	18.1 L (1106 in <sup>3</sup> )
Compression Ratio	14.5:1
Aspiration	Turbocharged Air-to-Air Aftercooled
Fuel Injection System	MEUI
Governor	Electronic ADEM™ A4

Image shown might not reflect actual configuration

Model	Standby	Prime	Emission Strategy
DE605E0	605 kVA, 484 ekW	550 kVA, 440 ekW	Low BSFC

### **PACKAGE PERFORMANCE**

Performance	Standby	Prime	
Frequency	50	50 Hz	
Genset power rating	605 kVA	550 kVA	
Genset power rating with fan @ 0.8 power factor	484 ekW	440 ekW	
Emissions	Low	BSFC	
Performance number	DM9820	DM9819	
Fuel Consumption			
100% load with fan, L/hr (gal/hr)	122.7 (32.4)	111 0 (29.3)	
75% load with fan, L/hr (gal/hr)	92.0 (24.3)	83.9 (22.2)	
50% load with fan, L/hr (gal/hr)	64.0 (16 9)	58.8 (15.5)	
25% load with fan , L/hr (gal/hr)	37.2 (9.8)	34.4 (9.1)	
Cooling System <sup>1</sup>			
Radiator air flow restriction (system), kPa (in. water)	0.12 (0.48)	0.12 (0.48)	
Radiator air flow, m <sup>3</sup> /min (cfm)	373 (13172)	373 (13172)	
Engine coolant capacity, L (gal)	20.8 (5.5)	20.8 (5.5)	
Radiator coolant capacity, L (gal)	34 (8.9)	34 (8.9)	
Total coolant capacity, L (gal)	54.8 (14.4)	54.8 (14.4)	
Inlet Air			
Combustion air inlet flow rate, m <sup>3</sup> /min (cfm)	31.6 (1117.5)	29.2 (1032.0)	
Max. allowable combustion air inlet temp, °C (°F)	49 (121)	47 (117)	
Exhaust System			
Exhaust stack gas temperature, °C (°F)	553.8 (1028.8)	543.1 (1009.6)	
Exhaust gas flow rate, m <sup>3</sup> /min (cfm)	92.1 (3251.0)	83.5 (2948.0)	
Exhaust system backpressure (maximum allowable), kPa (in. water)	10.0 (40.0)	10.0 (40.0)	
Exhaust System			
Heat rejection to jacket water, kW (Btu/min)	157 (8945)	146 (8309)	
Heat rejection to exhaust (total), kW (Btu/min)	449 (25525)	404 (22965)	
Heat rejection to aftercooler, kW (Btu/min)	76 (4313)	63 (3606)	
Heat rejection to atmosphere from engine, kW (Btu/min)	84 (4784)	78 (4438)	
Heat rejection to atmosphere from generator kW (Btu/min)	36 (2047)	31 (1763)	


## C18 Diesel Generator Sets Electric Power



Emissions (Nominal) <sup>2</sup>					
NOx, mg/Nm <sup>3</sup> (g/hp-hr)	3762.8 (7.7)			4029.2 (8.1)	
CO, mg/Nm <sup>3</sup> (g/hp-hr)	656.7 (1.3)		615.0 (1.2)		
HC, mg/Nm <sup>3</sup> (g/hp-hr)	3.2 (0.0)		3.3 (0.0)		
PM, mg/Nm <sup>3</sup> (g/hp-hr)	12.6 (0.0)		10.4 (0.0)		
Alternator <sup>3</sup>					
Voltages	380V	40	0V	415V	
Motor Starting Capability @ 30% Voltage Dip	1362 skVA	1507 skVA		1539 skVA	
Current	SB: 919A, PP: 811A	SB: 873A, PP: 794A		SB: 842A, PP: 765A	
Frame Size	A3325L4	A3325L4		A3325L4	
Excitation	SE	SE		SE	
Temperature Rise, °C (°F)	SB: 163°C, PP: 125°C				

SB: Standby PP: Prime Power.

### **WEIGHTS & DIMENSIONS**



Dim "A" mm (in)	Dim "B" mm (in)	Dim "C" mm (in)	Dry Weight kg (lb)
3830 (151)	1130 (44)	2156 (85)	3253 (7172)

Note: General configuration not to be used for installation. See general dimension drawings for detail.

#### **APPLICABLE CODES AND STANDARDS:**

AS1359, IEC60034-1, ISO3046, ISO8528, NEMA MG1-33, UKCA, CE, EAC. **Note:** Codes may not be available in all model configurations. Please consult your local Cat Dealer representative for availability.

**STANDBY:** Output available with varying load for the duration of the interruption of the normal source power. Average power output is 70% of the standby power rating. Typical operation is 200 hours per year, with maximum expected usage of 500 hours per year.

**PRIME:** Output available with varying load for an unlimited time. Average power output is 70% of the prime power rating. Typical peak demand is 100% of prime rated ekW with 10% overload capability for emergency use for a maximum of 1 hour in 12. Overload operation cannot exceed 25 hours per year

 $\label{eq:RATINGS: Ratings are based on SAE J1349 standard conditions. These ratings also apply at ISO3046 standard conditions.$ 

#### **DEFINITIONS AND CONDITIONS:**

<sup>1</sup> For ambient and altitude capabilities consult your Cat dealer. Air flow restriction (system) is added to existing restriction from factory.

C

- <sup>2</sup> Emissions data measurement procedures are consistent with those described in EPA CFR 40 Part 89, Subpart D & E and ISO8178-1 for measuring HC, CO, PM, NOx. Data shown is based on steady state operating conditions of 77° F, 28.42 in HG and number 2 diesel fuel with 35° API and LHV of 18,390 BTU/lb. The nominal emissions data shown is subject to instrumentation, measurement, facility and engine to engine variations. Emissions data is based on 100% load and thus cannot be used to compare to EPA regulations which use values based on a weighted cycle.
- <sup>3</sup> UL 2200 Listed packages may have oversized generators with a different temperature rise and motor starting characteristics. Generator temperature rise is based on a 40° C ambient per NEMA MG1-32.

# LET'S DO THE WORK.

#### www.cat.com/electricpower

©2024 Caterpillar.All rights reserved.

Materials and specifications are subject to change without notice. The International System of Units (SI) is used in this publication. CAT, CATERPILLAR, LET'S DO THE WORK, their respective logos, "Caterpillar Corporate Yellow" the "Power Edge" and Cat "Modern Hex" trade dress as well as corporate and product identity used herein, are trademarks of Caterpillar and may not be used without permission.