Cat[®] 3516E High Power Density (HPD) Diesel Generator Sets





Bore – mm (in)	170 (6.69)		
Stroke – mm (in)	215 (8.46)		
Displacement – L (in3)	78.1 (4766)		
Compression Ratio	14.0:1		
Aspiration	TA		
Fuel System	EUI		
Governor Type	ADEM™ A5		

Image shown may not reflect actual configuration

Standby	Mission Critical	Prime	Emissions Performance
50 Hz kVA (ekW)	50 Hz kVA (ekW)	50 Hz kVA (ekW)	
3000 (2400)	3000 (2400)	2725 (2180)	Tier 2 (EPA ESE) with Low NOx (< 2000mg NOx)

Features

Cat® Diesel Engine

- Tier 2 Certified (U.S. EPA Stationary Emergency) with < 2000 mg NOx emissions
- Reliable performance proven in thousands of applications worldwide
- Certified alternative fuels including Hydrotreated Vegetable Oil (HVO), Renewable Diesel (RD) and Hydrotreated Renewable Diesel (HRD) which meet EN 15940 or ASTM D975 can be used or blended with EN 590 diesel

Generator Set Package

- Accepts 100% block load in one step
- Meets NFPA 110 loading requirements
- Conforms to ISO 8528-5 G3 load acceptance requirements
- Reliability verified through torsional vibration, fuel consumption, oil consumption, transient performance, and endurance testing

Alternators

- Superior motor starting capability minimizes
 need for oversizing generator
- Designed to match performance and output characteristics of Cat diesel engines

Cooling System

- Cooling systems available to operate in ambient temperatures up to 50°C (122°F)
- Tested to ensure proper generator set cooling

Cat Energy Control System (ECS)

- · User-friendly interface and navigation
- Scalable system to meet a wide range of installation requirements
- Expansion modules and site specific programming for specific customer requirements
- Graphical touchscreen display
- Easily upgradeable

Warranty

- 24 months/1000-hour warranty for standby and mission critical ratings
- 12 months/unlimited hour warranty for prime and continuous ratings
- Extended service protection is available to provide extended coverage options

Worldwide Product Support

- Cat dealers have over 1,800 dealer branch stores operating in 200 countries
- Your local Cat dealer provides extensive post-sale support, including maintenance and repair agreements

Financing

- Caterpillar offers an array of financial products to help you succeed through financial service excellence
- Options include loans, finance lease, operating lease, working capital, and revolving line of credit
- Contact your local Cat dealer for availability in your region



Standard and Optional Equipment

Engine

Air Cleaner

Single element
 Dual element

Muffler

Industrial grade (15 dB)
 Critical grade (25 dB)
 Hospital grade (35 dB)

Starting

Standard batteries
Oversized batteries
Standard electric starter(s)
Dual electric starter(s)
Air starter(s)
Jacket water heater

Alternator

Output voltage

□ 400V
□ 6900V
□ 415V
□ 10000V
□ 3300V
□ 10500V
□ 6300V
□ 11000V
□ 6600V

Temperature Rise (over 40°C ambient)

□ 150°C □ 125°C/130°C

Winding type

Random woundForm wound

Excitation

Internal excitation (IE)Permanent magnet (PM)

Attachments

- Anti-condensation heater
- Stator and bearing temperature monitoring and protection

Power Termination

Туре

Bus bar
 Circuit breaker
 1600A
 2000A
 2500A
 3000A
 3200A
 4000A
 5000A
 UL
 IEC
 3-pole
 4-pole
 Manually operated
 Electrically operated

Trip Unit

LSI LSI-G LSIG-P

Control System

Controller

Cat ECS 100
 Cat ECS 200
 EMCP 4.4

Attachments

Local annunciator module
 Remote annunciator module
 Expansion I/O module
 Remote monitoring software

Charging

Battery charger – 10A
 Battery charger – 20A
 Battery charger – 35A

Vibration Isolators

RubberSpringSeismic rated

Cat Connect

Connectivity □ Ethernet □ Cellular

Extended Service Options

Terms

2 year (prime)
3 year
5 year
10 year

Coverage

Silver
Gold
Platinum

Platinum Plus

Ancillary Equipment

Automatic transfer switch (ATS)

- □ Paralleling switchgear
- □ Paralleling controls

Certifications

IBC seismic certification

- □ EU & GB Declaration of Conformity
- □ EU & GB Declaration of Incorporation
- Eurasian Conformity (EAC)
- Telecommunication Lab of China

Note: Some options may not be available on all models. Certifications may not be available with all model configurations. Consult factory for availability.




Package Performance

Performance	Sta	ndby	Missio	n Critical	Pr	ime
Frequency	50 Hz		50 Hz		50 Hz	
Gen set power rating with fan	2400 ekW		2400 ekW		2180 ekW	
Gen set power rating with fan @ 0.8 power factor	3000 kVA		3000 kVA		2725 kVA	
Emissions	Tier 2 (EPA ESE)		Tier 2 (EPA ESE)		Tier 2 (EPA ESE)	
Performance number	EM6277-00		EM6278-01		EM6335-01	
Fuel Consumption						
100% load with fan – L/hr (gal/hr)	643.1	(169.9)	643.1	(169.9)	599.5	(158.4)
75% load with fan – L/hr (gal/hr)	498.0	(131.6)	498.0	(131.6)	462.9	(122.3)
50% load with fan – L/hr (gal/hr)	344.3	(90.9)	344.3	(90.9)	312.0	(82.4)
25% load with fan – L/hr (gal/hr)	192.0	(50.7)	192.0	(50.7)	178.6	(47.2)
Cooling System						
Radiator air flow restriction (system) – kPa (in. water)	0.12	(0.48)	0.12	(0.48)	0.12	(0.48)
Radiator air flow – m³/min (cfm)	2879	(101671)	2879	(101671)	2879	(101671)
Engine coolant capacity – L (gal)	233.0	(61.6)	233.0	(61.6)	233.0	(61.6)
Radiator coolant capacity – L (gal)	202.0	(53.4)	202.0	(53.4)	202.0	(53.4)
Total coolant capacity – L (gal)	435.0	(115.0)	435.0	(115.0)	435.0	(115.0)
Inlet Air						
Combustion air inlet flow rate – m³/min (cfm)	207.8	(7336.0)	207.8	(7336.0)	202.0	(7131.5)
Exhaust System						
Exhaust stack gas temperature – °C (°F)	495.8	(924.4)	495.8	(924.4)	488.3	(911.0)
Exhaust gas flow rate – m³/min (cfm)	545.2	(19249.8)	545.2	(19249.8)	522.6	(18453.9)
Exhaust system backpressure (maximum allowable) – kPa (in. water)	6.7	(27.0)	6.7	(27.0)	6.7	(27.0)
Heat Rejection						
Heat rejection to jacket water – kW (Btu/min)	837	(47625)	837	(47625)	787	(44735)
Heat rejection to exhaust (total) - kW (Btu/min)	2609	(148361)	2609	(148361)	2477	(140872)
Heat rejection to aftercooler - kW (Btu/min)	799	(45434)	799	(45434)	741	(42129)
Heat rejection to atmosphere from engine – kW (Btu/min)	164	(9307)	164	(9307)	158	(8979)
Heat rejection from alternator – kW (Btu/min)	104	(5914)	104	(5914)	79	(4498)
Emissions* (Nominal)						
NOx mg/Nm ³ (g/hp-h)	1755.0	(3.82)	1755.0	(3.82)	1569.0	(3.51)
CO mg/Nm ³ (g/hp-h)	372.0	(0.81)	372.0	(0.81)	273.9	(0.61)
HC mg/Nm ³ (g/hp-h)	12.4	(0.03)	12.4	(0.03)	14.0	(0.04)
PM mg/Nm ³ (g/hp-h)	23.5	(0.06)	23.5	(0.06)	19.4	(0.05)
Emissions* (Potential Site Variation)						
NOx mg/Nm ³ (g/hp-h)	1983.2	(4.32)	1983.2	(4.32)	1773.0	(3.97)
CO mg/Nm ³ (g/hp-h)	557.9	(1.22)	557.9	(1.22)	410.9	(0.92)
HC mg/Nm ³ (g/hp-h)	13.3	(0.03)	13.3	(0.03)	15.0	(0.04)
PM mg/Nm ³ (g/hp-h)	32.9	(0.09)	32.9	(0.09)	27.2	(0.07)

 $^{*}mg/Nm^{3}$ levels are corrected to 5% O₂. Contact your local Cat dealer for further information.



Weights and Dimensions



Dim "A"	Dim "B"	Dim "C"	Dry Weight
mm (in)	mm (in)	mm (in)	_{kg (lb)}
7954 (313.1)	2640 (104.0)	3342 (131.6)	20 380 (44,930)

Note: For reference only. Do not use for installation design. Contact your local Cat dealer for precise weights and dimensions.

Ratings Definitions

Standby

Output available with varying load for the duration of the interruption of the normal source power. Average power output is 70% of the standby rated ekW. Typical operation is 200 hours per year, with maximum expected usage of 500 hours per year.

Mission Critical

Output available with varying load for the duration of the interruption of the normal source power. Average power output is 85% of the mission critical rated ekW. Typical peak demand up to 100% of rated ekW for up to 5% of the operating time. Typical operation is 200 hours per year, with maximum expected usage of 500 hours per year.

Prime

Output available with varying load for an unlimited time. Average power output is 70% of the prime rated ekW. Typical peak demand is 100% of prime rated ekW with 10% overload capability for emergency use for a maximum of 1 hour in 12. Overload operation cannot exceed 25 hours per year.

Applicable Codes and Standards

AS 1359, IBC, IEC 60034-1, ISO 3046, ISO 8528, NEMA MG1-22, NEMA MG1-33, 2014/35/EU, 2006/42/EC, 2014/30/EU and facilitates compliance to NFPA 37, NFPA 70, NFPA 99, NFPA 110, GB/T 2820.

Note: Codes may not be available in all model configurations. Please consult your local Cat dealer for availability.

Data Center Applications

- All ratings Tier III/Tier IV compliant per Uptime Institute requirements.
- All ratings ANSI/TIA-942 compliant for Rated-1 through Rated-4 data centers.

Fuel Rates

Fuel consumption reported in accordance with ISO 3046-1, based on fuel oil of 35° API [$16^{\circ}C$ ($60^{\circ}F$)] gravity having an LHV of 42,780 kJ/kg (18,390 Btu/lb) when used at $15^{\circ}C$ ($59^{\circ}F$) and weighing 850 g/liter (7.0936 lbs/U.S. gal.) All fuel consumption values refer to rated engine power.

www.cat.com/electricpower ©2024 Caterpillar All rights reserved.

Materials and specifications are subject to change without notice. The International System of Units (SI) is used in this publication.

CAT, CATERPILLAR, LET'S DO THE WORK, their respective logos, "Caterpillar Corporate Yellow", the "Power Edge" and Cat "Modern Hex" trade dress as well as corporate and product identity used herein, are trademarks of Caterpillar and may not be used without permission.