

# Cat® C18

## Diesel Generator Sets



### Standby & Prime: 50 Hz



Engine Model	Cat® C18 ATAAC™ In-line 6, 4-cycle diesel
Bore x Stroke	145 mm x 183 mm (5.7 in x 7.2 in)
Displacement	18.13 L (1106.3 in³)
Compression Ratio	14:1
Aspiration	Turbocharged Air-to-Air Aftercooled
Fuel Injection System	Electronic Unit Injection
Governor	Electronic ADEM™ A4 - G3 Class* capable

Image shown might not reflect actual configuration


Model	Standby	Prime	Emissions Strategy
DE780E0	780 kVA	706 kVA	Low BSFC

### PACKAGE PERFORMANCE

Performance	Standby	Prime
Frequency	50 Hz	
Genset Power Rating	780 kVA	706 kVA
Genset power rating with fan @ 0.8 power factor	624 ekW	564 ekW
Emissions	Low BSFC	
Performance Number	EM3823	EM3824
<b>Fuel Consumption</b>		
100% load with fan, L/hr (gal/hr)	157 (41.4)	142.1 (37.5)
75% load with fan, L/hr (gal/hr)	116.3 (30.7)	105.2 (27.7)
50% load with fan, L/hr (gal/hr)	80.5 (21.2)	74.1 (19.5)
25% load with fan, L/hr (gal/hr)	46.9 (12.3)	43.7 (11.5)
<b>Cooling System<sup>1</sup></b>		
Radiator air flow restriction (system), kPa (in. Water)	0.12 (0.48)	0.12 (0.48)
Radiator air flow, m³/min (cfm)	853 (30123)	853 (30123)
Engine coolant capacity, L (gal)	21 (5.5)	21 (5.5)
Radiator coolant capacity, L (gal)	89 (23.5)	89 (23.5)
Total coolant capacity, L (gal)	110 (29.1)	110 (29.1)
<b>Inlet Air</b>		
Combustion air inlet flow rate, m³/min (cfm)	56 (1977)	52.4 (1850)
Max. allowable air intake restriction (kPa)	3.7 (clean element) / 6.2 (dirty element)	
<b>Exhaust System</b>		
Exhaust stack gas temperature, °C (°F)	406 (762)	394 (741)
Exhaust gas flow rate, m³/min (cfm)	131 (4662)	120 (4202)
Exhaust system backpressure (maximum allowable) kPa (in. water)	8.5 (2.5)	8.5 (2.5)
<b>Heat Rejection</b>		
Heat rejection to jacket water, kW (Btu/min)	180 (10236)	167 (9497)
Heat rejection to exhaust (total) kW (Btu/min)	553 (31449)	497 (28264)
Heat rejection to aftercooler, kW (Btu/min)	192 (10919)	170 (9667)
Heat rejection to atmosphere from engine, kW (Btu/min)	91.1 (5180)	85 (4833)

Emissions <sup>2</sup> (Nominal-CORR 5% O <sub>2</sub> )	Standby			Prime		
NO <sub>x</sub> , mg/Nm <sup>3</sup> (g/hp-hr)	3080.2 (6.54)			2988 (6.31)		
CO, mg/Nm <sup>3</sup> (g/hp-hr)	161.9 (0.35)			82.6 (0.17)		
HC, mg/Nm <sup>3</sup> (g/hp-hr)	31.8 (0.08)			14 (0.03)		
PM, mg/Nm <sup>3</sup> (g/hp-hr)	11.3 (0.03)			9.3 (0.02)		
Alternator <sup>3</sup>						
Voltages	415 V	400 V	380 V	415 V	400 V	380 V
Motor starting capability @ 30% Voltage Dip & 0.6 P.F	2278 skVA	2128 skVA	1935 skVA	2278 skVA	2128 skVA	1935 skVA
Current	1085.1 amps	1125.8 amps	1185.1 amps	982.2 amps	1019 amps	1072 amps
Frame Size	LC7224J	LC7224J	LC7224J	LC7224J	LC7224J	LC7224J
Excitation	AREP	AREP	AREP	AREP	AREP	AREP
Temperature Rise	163°C	150°C	163°C	125°C	125°C	125°C

## WEIGHTS & DIMENSIONS



Length "A" mm (in)	Width "B" mm (in)	Height "C" mm (in)	Dry Weight Kg (lb)
4130 (163)	1689 (67)	2570 (101)	4532 (9991)

**Note:** General configuration not to be used for installation. See general dimension drawings for detail.

### APPLICABLE CODES AND STANDARDS:

AS1359, IEC60034-1, ISO3046, ISO8528, NEMA MG1-33, EAC, CE, UKCA  
 Note: Codes may not be available in all model configurations. Please consult your local Cat Dealer representative for availability.

**STANDBY:** Output available with varying load for the duration of the interruption of the normal source power. Average power output is 70% of the standby power rating. Typical operation is 200 hours per year, with maximum expected usage of 500 hours per year.

**PRIME:** Output available with varying load for an unlimited time. Average power output is 70% of the prime power rating. Typical peak demand is 100% of prime rated kW with 10% overload capability for emergency use for a maximum of 1 hour in 12. Overload operation cannot exceed 25 hours per year.

**RATINGS:** Ratings are based on SAE J1349 standard conditions. These ratings also apply at ISO3046 standard conditions.

### DEFINITIONS AND CONDITIONS

<sup>1</sup> For ambient and altitude capabilities consult your Cat dealer. Air flow restriction (system) is added to existing restriction from factory.

<sup>2</sup> Emissions data measurement procedures are consistent with those described in EPA CFR 40 Part 89, Subpart D & E and ISO8178-1 for measuring HC, CO, PM, NO<sub>x</sub>. Data shown is based on steady state operating conditions of 77° F, 28.42 in HG and number 2 diesel fuel with 35° API and LHV of 18,390 BTU/lb. The nominal emissions data shown is subject to instrumentation, measurement, facility and engine to engine variations. Emissions data is based on 100% load and thus cannot be used to compare to EPA regulations which use values based on a weighted cycle.

<sup>3</sup> Generator temperature rise is based on a 40° C ambient per IEC60034-1.

\* Governing Class capability as per ISO-8528-5.

# LET'S DO THE WORK.™

[www.cat.com/electricpower](http://www.cat.com/electricpower)

©2024 Caterpillar  
All rights reserved.

Materials and specifications are subject to change without notice.

The International System of Units (SI) is used in this publication. CAT, CATERPILLAR, LET'S DO THE WORK, their respective logos, "Caterpillar Corporate Yellow", the "Power Edge" and Cat "Modern Hex" trade dress as well as corporate and product identity used herein, are trademarks of Caterpillar and may not be used without permission.