

# Cat® XQ60 Rental Generator Set



**Prime 46 ekW, 57.5 kVA  
U.S. EPA Tier 4 Final 60 Hz  
1800 RPM**



Image shown may not reflect actual configuration.

## Specifications

Generator	Frequency	Voltage LL/LN	Prime ekW (kVA)	Phase	Amp (A)
Standard	60 Hz	480/277 V	46 (57.5)	3-Phase	69.2
		208/120 V	46 (57.5)	3-Phase	159.6
		240/120 V	39 (39)	1-Phase	162.5
Optional	60 Hz	600/349 V	46 (57.5)	3-Phase	55.3
		480/277 V	46 (57.5)	3-Phase	69.2
		208/120 V	42 (52.5)	3-Phase	145.7
		240/120 V	33 (33)	1-Phase	137.5

Cat® C3.6 Diesel Engine	Metric	Imperial (English)
Configuration	I-4, 4-stroke diesel	
Bore	98 mm	3.85 in
Stroke	120 mm	4.72 in
Displacement	3.6 L	219 in <sup>3</sup>
Aspiration	Turbocharged-Aftercooled (TA)	
Compression Ratio	17:1	
Engine Speed	1800 rpm	
Governor Type	Electronic	
Governor Class	ISO 8528 G2	
Maximum Power at rated speed – kW (hp) Prime	50.4	67.5

## Benefits & Features

### Fuel/Emissions Strategy

- Meets U.S. EPA Tier 4 Final emission standards and CARB certified for non-road mobile applications at all 60 Hz ratings

### Cat® C3.6 Diesel Engine

- Four-stroke diesel engine combines performance and excellent fuel economy with minimum weight
- On-engine aftertreatment consists of Diesel Oxidation Catalyst (DOC), and Diesel Particle Filter (DPF) for service-free operation
- Load management system
- 500-hour oil change interval
- Electronic engine controls
- Engine block heater 120 VAC

### Cat LC Series Generator

- Matched to the performance and output characteristics of Cat diesel engines
- Class H Insulation

### XQCP Control Panel

- Electronic control panel provides power metering, protective relaying, engine, and generator parameter viewing, and expanded AC metering
- Four lines back-lit LCD text display
- Simple, user-friendly interface and navigation
- Integrates with the Automatic Voltage Regulator (AVR) to provide precise control, excellent block loading, and constant voltage

### Design Features

- 110% spill containment of all engine fluids
- Nonmetallic fuel tank provides > 24-hour run time at 75% prime load
- Two-way valve and external fuel ports to easily switch between onboard and external fuel source
- Solar battery maintainer

### Sound-attenuated Enclosure

- Rugged, corrosion-resistant construction:
  - Galvannealed, sheet steel body panels with zinc phosphate pre-treatment prior to polyester powder coating
  - Stainless steel hinges
- Excellent access for service and maintenance:
  - Two doors on each side, and one rear door for power distribution and control panel access
  - Lube oil and coolant drains piped to exterior of the enclosure
- Security and safety features:
  - Control panel located behind rear access door with safety-glass viewing window
  - Padlockable latches on all access doors
  - Exterior emergency stop (E-stop) button
- Single point lifting

### Standard Controls and Power Distribution

- Three-position switch for easy selection of desired output (480/277 V 3-phase, 208/120 V 3-phase, or 240/120 V single phase)
- Controls, sockets, and power distribution all accessible via rear access door
- Hinged door over main bus bars with safety switch to trip breaker

### Asset Monitoring and Management

- Cat Connect hardware provides two-way communication for remote control and equipment monitoring via cellular or hardwired network
- Customer-defined, equipment-based real-time status updates and alerts
- Flexible and customer-configurable user interface
- GPS provides asset location and geo-fencing

### Options

- Generator anti-condensation heater
- PMG (Permanent Magnet Generator)
- Battery charger
- Trailer brake (electric or hydraulic)
- Trailer hitch (2-in. ball, 2-5/16-in. ball, or pintle)
- 208V 3-phase sockets with breakers

## Standard Equipment

### Engine

- Cat C3.6 , heavy-duty, U.S. EPA Tier 4 Final certified diesel engine with load management system.
- Engine-mounted DOC plus DPF canister
- Block heater, 110-120 VAC
- Requires Ultra Low Sulfur Diesel (ULSD) fuel
- Engine electrical system:
  - 12 V, DC electrical system
  - 85 A, DC charging alternator
- Electronic governor and engine controls
- Oil pressure, coolant temperature, and coolant level shutdown switches
- Engine filtration system:
  - Cartridge-type air filter with service indicator
  - Cartridge-type fuel filter with upstream pre-filter and water separator; requires ULSD fuel
- Spin-on, full-flow lube oil filter; requires API CJ-4 lube oil

### Generator and Voltage Regulation

- Screen protected and drip-proof (IP23), self-regulating, 12-lead, 4-pole, brushless generator
- Sealed-for-life bearing
- Electrical design in accordance with IEC 60034-1, EN 61000-6, NEMA MG 1-22, and CSA
- Self-excited for self protection against short circuits
- Voltage selection switch (3-position) mounted to generator terminal box
  - Optional
  - Anti-condensation, space heater, 60-Watt, 110- 120 VAC
- Insulation system:
  - Class H insulation system
  - Windings impregnated in a thermo-setting moisture-, oil-, and acid-resisting varnish
  - Heavy coat of anti-tracking varnish for additional protection against moisture or condensation
- AVR D350:
  - Simplified operation and troubleshooting
  - Equipped with NFC technology for communication and configuration purposes
  - Fully supported by Cat ET service tool
- Waveform distortion, THF, and TIF factors:
  - Total distortion of voltage waveform with open circuit between phases, or phase and neutral, on the order of 1.8 total distortion < 4%, on a 3- phase, balanced, harmonic-free load
  - Total distortion < 2%, under no load
  - Waveform: NEMA (TIF < 50)
  - 2/3 pitch factor standard on all stator windings

### Generator Set Packaging

- Base frame and containment tray:
  - Heavy-duty, fabricated steel base frame with specially-designed lifting points
  - Spill containment tray mounted to base frame, with leak-detection switch
  - Electronic fuel gauge
- Canopy:
  - Sound attenuated to 67 dBA at 7m (23 ft)
  - Two doors on each side, one rear door for power distribution and control panel access
- Cooling system:
  - Cooling system provides 43°C (109°F) ambient capability at 500 m (2,460 ft) above sea level
- Electrical system:
  - 12 V, DC electrical system
  - 850 CCA, maintenance-free, wet battery
  - Battery disconnect switch, lockable
  - Solar battery charger with solar array
  - Resettable, switch-style circuit breakers (DC circuit)
  - Optional 12 V, 10 A battery charger, constant voltage, UL Listed
- Engine and generator mounting:
  - Engine and generator directly coupled by SAE flange
  - Engine flywheel flexibly coupled to the generator rotor, with full torsional analysis completed to ensure no harmful vibration will occur in the assembly
  - Anti-vibration pads between engine/generator feet and base frame
- Fuel system:
  - Cross-linked polyethylene (XLPE) fuel tank
  - 24-hour runtime @ 75% prime load
  - 2-position valves and external ports (1/4-in.NPT) allow connection of an auxiliary fuel source
- CSA 22.2 Certified

## Standard Equipment *(continued)*

### Generator Controls and Power Distribution

- XQCP, digital generator set controller, mounted behind a hinged, lockable door with viewing window
- Circuit breaker: 3-pole molded case breaker, 175A, UL Listed and CSA Certified with shunt trip
- Safety switch on hinged main bus cover – trips breaker if cover is opened
- Two-wire, remote start-stop terminals
- Customer auxiliary power connections:
  - Two – 250 V, 50A California-style, twist locking input receptacles
  - Two – 120 V, 20A duplex receptacles with GFCI\*
  - Each receptacle protected by a miniature circuit breaker, which also acts as an on/off switch
- Main customer connections:
  - Tin-plated copper bus bars with phase separators, located behind a protective door with shunt trip switch
  - Bus bars sized for full load capacity of generator set at 0.8 power factor
- Optional:
  - Two NEMA output receptacles

### Quality and Product Support

- Factory load-testing of complete generator set
- Factory test certificate available upon request
- Equipment meets the following standards: BS 4999, BS 5000, BS 5514, IEC 60034, EN 61000-6, NEMA MG 1-22 & CSA
- Full set of operation and maintenance manuals

### 600 V Generator

- Includes 600 V generator and 4-position rotary switch for easy selection of desired output
- Available voltages include:
  - o 3-phase (600/347 Volt, 480/277 Volt, 208/120 Volt)
  - o 1-phase (240/120 Volt)
- Voltage at receptacle is 120 V when switch is in 240/120 and 208 positions, and 139 V in 480 V position.

**Technical Data**

Cat Generator		
Frame Size	LC1514P	
Pitch	0.6667	
No. of poles	4	
Insulation	Class H	
Enclosure	Drip proof IP23	
Voltage regulation	± 0.25% at steady state from no load to full load	
Frequency regulation	± 0.25% for constant load from no load to full load	
Waveform deviation	THD <4%	
Overspeed limit	2250 rpm	
Available voltages	Standard	Switchable voltage output: 480/277V, 3-phase; 208/120V, 3-phase; 240/120V, single-phase
	Optional	N/A


Cat Generator Set – 1800 rpm/60 Hz		
	Units	Prime
<b>Power Rating</b>	ekW (kVA)	46 (57.5)
<b>Performance Specification</b>		
<b>Lubricating System</b> Capacity oil	L (gal)	9 (2.38)
<b>Fuel System</b> Fuel consumption — 100% Load 75% Load 50% Load Fuel tank capacity	L/hr (gal/hr) L/hr (gal/hr) L/hr (gal/hr) L (gal)	12.4 (3.3) 9.77 (2.6) 7.1 (1.9) 303 (80)
<b>ISO Prime Running Time</b>	Hours	>24
<b>Cooling System</b> Radiator system capacity including engine Heat rejected to coolant at rated power	L (U.S. gal) kW (Btu/min)	13.5 (3.57) 37.3 (2123)
<b>Air Requirements</b> Combustion air flow Radiator cooling air Generator cooling air	m³/min (cfm) m³/min (cfm) m³/min (cfm)	3.8 (134) 79.4 (2805) 7.8 (275)
<b>Noise Rating**</b> with enclosure at 7 meters (23 feet)	dB(A)	67

\*\*Package fuel consumption and sound levels are for reference only.

## Dimensions and Weights

Model	Length (L) mm (in)	Width (W) mm (in)	Height (H) mm (in)	With Lube Oil & Coolant kg (lb)	With Fuel, Lube Oil & Coolant kg (lb)
XQ60 with trailer (electric brakes)	3980 (156.7)	1725 (67.9)	1947 (76.6)	1636 (3607)	1896 (4180)
XQ60 with trailer (hydraulic brakes)	4059 (159.8)	1725 (67.9)	1947 (76.6)	1641 (3618)	1901 (4191)
XQ60 without trailer	2705 (106.5)	1049 (41.3)	1658 (65.3)	1423 (3137)	1683 (3710)


## General Layout



XQ60 GENERAL LAYOUT DRAWING

### Control Panel and Power Distribution Layout

Item	Description																
1	Steel enclosure with hinged, lockable door (not shown)																
2	Circuit breakers for receptacles																
3	Emergency stop																
4	Single-phase GFCI duplex receptacles (20A @ 120V)																
5	Two-wire remote start terminals																
6A	2 x Single-phase, California-style twist-lock receptacles, 50A @ 208V phase-to-phase, 120V phase to neutral, or 240/120V single phase when in that voltage position																
6B	2 x NEMA locking output receptacles (Optional)																
7	1 x Single-phase NEMA locking input receptacle (30A @ 120V) to power optional block heater, battery charger, and generator space heater																
8	HEST and DPF lamp																
9	Glow plug lamp	10	XQCP digital generator set controller	11	Potentiometer for voltage adjustment	12	Cat ET service tool connector	13	Circuit breaker, 3-pole molded case, 175A	14	Main bus connection (bus bars attached to breaker) behind door and viewing window	15	Bus bar viewing window w/ phase diagram film	16	Quarter-turn door lock	17	Breaker trip door switch
10	XQCP digital generator set controller																
11	Potentiometer for voltage adjustment																
12	Cat ET service tool connector																
13	Circuit breaker, 3-pole molded case, 175A																
14	Main bus connection (bus bars attached to breaker) behind door and viewing window																
15	Bus bar viewing window w/ phase diagram film																
16	Quarter-turn door lock																
17	Breaker trip door switch																



### Ratings Definition

**Prime** – Output available with varying load for an unlimited time. Average power output is 70% of the prime power rating. Typical peak demand is 100% of prime rated kW.

[www.cat.com/electricpower](http://www.cat.com/electricpower)

©2026 Caterpillar  
All rights reserved.

Materials and specifications are subject to change without notice.

The International System of Units (SI) is used in this publication.

CAT, CATERPILLAR, LET'S DO THE WORK, their respective logos, "Caterpillar Corporate Yellow" the "Power Edge" and Cat "Modern Hex" trade dress as well as corporate and product identity used herein, are trademarks of Caterpillar and may not be used without permission.