



Picture shown may not reflect actual configuration

Features

- Contact wear monitoring including real-time status and predicted contact end-of-life
- Minimum 3 embedded temperature sensors
- · High current protection and alarm
- Color touchscreen HMI with intuitive menu navigation, measurements display, and 250 event log
- Wide 200-480V range with auto-configuration of system settings for 100-1200A range

- Ekip Connect software helps reduce commissioning time by 50%
- Five factory programmed packages available; IO can be re-programmed in seconds
- High time-based withstand and closing ratings (WCR) and even higher coordinated WCR
- · Short-time withstand ratings in every frame
- Fast controller response to outage recovery and fast switching (<50ms)

Cat[®] CBS Series

The CBS Series is equipped with an intuitive fullcolor touchscreen HMI and is compatible with Ekip Connect software to ease commissioning and operation, maximize flexibility with a wide 200-480V range and an array of standard programmable functions and IO, and finally, simplify service with unique modular components that are easier to stock and replace in the field.

CBS Series is built for high performance and incorporates design elements for simple service. Taking it to the next level, this advanced ATS range takes a proactive outage mitigation approach by monitoring temperature and contact health 24/7 and alerting to any anomalies, helping to ensure power keeps flowing.

The CBS Series lineup has unique advances in safety with faster switching and no line voltages connected at the door.



30-1200A Open And Delayed Transition Construction



- 1. Automatic transfer switch
- 2. Bypass transfer switch (operates as automatic when primary ATS is out of circuit)
- 3. Embedded ATS control units and mechanisms
- 4. HMI unit, type CBS (LvI 4) color touchscreen interface, one HMI for ATS and one for Bypass, providing bypass status indication
- 5. Bypass-isolation mechanism interface
- 6. Protective barriers (terminals behind top metal barrier)
- 7. Place for ATS connectivity modules (com and signaling), and auxiliary contact connections
- 8. Programming port, for Ekip Programming module and Ekip Connect software



1600-3000A Construction



- 1. Automatic transfer switch power panel & mechanism
- 2. HMI unit, type CBS (LvI 4) color touchscreen interface
- 3. ATS / Bypass-isolation controls cabinet location of customer control connections and connectivity modules (com and signaling)
- 4. TruCONTROL ATS controller
- 5. Bypass-isolation indication panel
- 6. Handle connection points for manual operation
- 7. Handle for ATS manual operation
- 8. ATS position indicator
- 9. Bypass-isolation mechanism interface



Cat CBS Series Features

System Information					
Ampere sizes available	Open transition	UL: 100-3000A			
	Delayed transition UL: 100-300				
	Closed transition UL:1000-3000A				
Rated voltage	200-480Vac				
Rated frequency	50 / 60 Hz				
Phase system	Single and Three				
Number of poles	2, 3 and 4				
Neutral configuration					
Switched neutral	Yes				
Overlapping neutral available	30-1200A only				
Solid neutral	Yes				
Product type					
Open transition (I-II)	Yes				
Delayed transition (I-O-II)	Yes				
Closed transition (I-O-II)	Yes				
Voltage and frequency settings	I.				
Pick up Voltage Source 1**	71-99%. 101-119%				
Drop out Voltage Source 1*	70-98%. 102-120%				
Pick up Voltage Source 2**	71-99%. 101-119%				
Drop out Voltage Source 2*	70-98%. 102-120%				
Pick up Frequency Source 1	80.5-99.5%. 100.5-119.5	%			
Drop out Frequency Source 1	80-99% 101-120%				
Pick up Frequency Source 2	80.5-99.5%, 100.5-119, 5	5%			
Drop out Frequency Source 2	80-99% 101-120%				
Time delay settings	· · · · · · · · · · · · · · · · · · ·				
Override momentary Source 1 Outage, sec	0-60				
Transfer from Source 1 to Source 2. sec	0-3600				
Override momentary Source 2 Outage, sec	0-60				
Transfer from Source 2 to Source 1. min	0-120				
Generator stop delay, min	0-60				
Center-OFF delay, sec (Delayed Transition Type)	0-300				
Pre-transfer delay S1 to S2, sec	0-300				
Post-transfer delay S1 to S2, sec	0-300				
Pre-transfer delay S2 to S1, sec	0-300				
Post-transfer delay S2 to S1, sec	0-300				
Elevator Pre-signal delay S1 to S2, sec	0-60				
Elevator Post-signal delay S1 to S2, sec	0-60				
Elevator Pre-signal delay S2 to S1, sec	0-60				
Elevator Post-signal delay S2 to S1, sec	0-60				
Load shed delay, sec	0-300				
Source failure detections					
No voltage	Yes				
Undervoltage	Yes				
Overvoltage	Yes				
Phase missing	Yes				
Voltage unbalance	Yes				
Invalid frequency	Yes				
Incorrect phase sequence	Yes				

* Drop out voltage settings possible as low as 70% for 240V-480V systems. ** Minimum pick up rating for 1600-3000A designs is 85%



Additional Features	
Controls	Color touchscreen
LED indications for ATS, S1 and S2 status	Yes
Programmable digital inputs/outputs	Yes
Auto config (voltage, frequency, phase system)	Yes
Source priority	Source 1/2, No priority
Manual re-transfer	Yes
In-phase monitor (synchro check)	Yes
Genset exercising: on-load, off-load	Yes
In-built power meter module	Yes
Load shedding	Yes
Real time clock	Yes
Event log	Yes
Predictive maintenance	Yes
Voltage and current harmonics measuring	Yes
Field-mount accessories	
Auxiliary contacts for position indication	Yes
Digital input/output modules (factory programmed)	Yes
12-24 Vdc aux supply module for controller	Yes
Communication modules	Yes
Connectivity capability	
Modbus RTU (RS-485)	Yes
Modbus/TCP	Yes
Profibus DP	Yes
ProfiNet	Yes
DeviceNet	Yes
Ethernet IP	Yes
For applications	
Utility - Utility	Yes
Utility - Generator (minimum size 20kVA)	Yes
UL short circuit withstand ratings	
Coordinated breaker WCR	Yes
Time-based WCR	Yes
Short-time ratings	Yes



Tuno	Eurotions	Pre-configured						
туре		IO packa	ges					
Input functions		Base Plus ¹ Controls Flex ¹						
No function	Input disabled.	2	-	-	-	-		
Emergency Stop	Transfers to O position in delayed	-	-	-	-	-		
	transition I-O-II type switches. Disables							
	automatic control mode in both delayed							
	and open transition types.							
Remote Test On	Start/stop test on load sequence in rising	-	1	1	1	1		
Load / Peak shave	(NO) or falling (NC) edge of the input							
	signal.							
Remote Test Off	Start/stop test off load sequence in rising	-	-	-	-	-		
Load	(NO) or falling (NC) edge of the input							
	signal.							
Inhibit AUTO	Prevent switch control operations,	-	-	1	-	1		
Mode	configuration, test sequences and							
	generator start in case of priority source							
	failure.							
Manual	Disables automatic transfer back to	-	-	1	1	1		
Retransfer	priority source.							
Source Priority S1	Sets priority for source 1 in transformer-	-	-	-	-	-		
	transformer application.							
Source Priority S2	Sets priority for source 2 in transformer-	-	-	-	-	-		
	transformer application.							
Inhibit Transfer	Disables automatic transfer from priority	-	-	1	-	1		
	source to non-priority source.							
Bypass Running	Bypass any currently running time delay.	-	-	1	-	-		
Time Delays				42	4.2	42		
Load Shed ATS to	Allows back-up generator to signal to AIS	-	-	12	12	12		
S1	to move to S1 to prevent overload. Stays							
	in S1 if S1 restores and input removed.			42	43	43		
Load Shed ATS to	Allows back-up generator to signal to AIS	-	-	13	13	13		
OFF	to move to O to prevent overload. If S1							
	restores, transfer to S1 will occur even it							
Domoto Control	Input is maintained.							
Remote Control	Iransfer to SI when active. Overridden by	-	-	-	-	-		
to SI Remete Centrel	Transfer to O position when active							
Remote Control	Transfer to O position when active.	-	-	-	-	-		
LO UFF	Transfor to \$2 when active Overridden by							
	activated 'Pamota Control to OEE' or	-	-	-	-	-		
10.52	Bomata Control to S1' signals							
Reset Alarm	Reset any active switch control alarms		_					
Reset Aldrin	(open I failure, close I failure, open II	_	_	_				
	failure, close II failure)							
Manual-Auto	Toggle automatic/HMI control mode		_	_	_	_		
Mode	input is active only in rising falling edge	_	_	_	_			
widde	according to contact type							
	Laccording to contact type.		ļ	L		1		

1. Three additional inputs available if selector switch option not selected

Open transition configurations only
Delayed transition configurations only



Туре	Type Functions		Pre-configured				
Output functions	Base	Plus ⁴	Controls ^₄	Flex ⁴	Motor ⁴		
No Function	Output disabled.	1	-	-	-	-	
Alarm / Product availability	Signals any active alarms or ATS being disabled for automatic transfer operations.	-	-	-	-	-	
Load Connected to S1	Signals switch in position I.	-	-	-	-	-	
Load Disconnected	Signals switch in position O.	-	-	-	-	1	
Load Connected to S2	Switch in position II.	-	-	-	-	-	
Pre-transfer Signal	Signal is activated and transfer is delayed according to pre-transfer delay. Signal is kept activated according to post-transfer delay after transfer.	-	-	1	1	2	
Source 1 Available	Signals no anomalies in S1 voltage supply.	-	1	1	1	1	
Source 2 Available	Signals no anomalies in S2 voltage supply.	-	1	1	1	1	
Load Shed 1	Used for shedding non-essential loads before transferring to non-priority source. The signal is activated before transferring to non-priority source according to load shed delay and kept activated until load is transferred back to priority source.	-	-	-	-	-	
Elevator pre- signal	The signal is activated and transfer is delayed according to Elevator pre-signal delay. The signal is kept activated according to Elevator post-signal delay after transfer.	-	-	1	1	1	

4. One additional output available if transfer alarm option not selected



Cat CBS Series technical data 100-200A

		Switch size (A)				
Data according to UL1008	Units	100	125	160	200	
Rated operational voltage	Vac		200 -	- 480		
Operating voltage range	Vac		160 -	- 576		
Rated frequency	Hz		50	-60		
Emergency systems - Motor loads or total system	Α	100	125	160	200	
Optional standby systems - Motor loads or total system	А	100	125	160	200	
Short-circuit withstand/closing and short-time current ratings	kA	Se	e table on f	ollowing pa	ge	
Contact transfer time I-II, II-I Load interrupting time	ms		<"	50		
Operating transfer time I-II, II-I	ms		<500			
ATS current draw during transfer / time duration	A / ms	ns 35 / <110				
Suitable for applications		Utility - Utility,				
		Utility - Generator				
ATS-Bypass orientation			Bottom	and Top		

Cat CBS Series technical data 260-1200A

		Switch size (A)					
Data according to UL1008	Units	260	400	600	800	1000	1200
Rated operational voltage	Vac			200 - 4	480		
Operating voltage range	Vac			160 - 5	576		
Rated frequency	Hz			50-6	0		
Emergency systems - Motor loads or total system	A	260	400	600	800	1000	1200
Optional standby systems - Motor loads or total system	A	260	400	600	800	1000	1200
Short-circuit withstand/closing and short-time current ratings	kA	See table on following page					
Contact transfer time I-II, II-I Load interrupting time	ms			<50)		
Operating transfer time I-II, II-I	ms			<50	0		
ATS current draw during transfer / time duration	A / ms	ms 35/<110 40/<130					
Suitable for applications			Utility - Utility				
			Utili	ty - Ge	nerato	or	
ATS-Bypass orientation Bottom and Top)			

Cat CBS Series technical data 1600-3000A

		Switch size (A)				
Data according to UL1008	Units	1600	2000	2600	3000	
Rated operational voltage	Vac		200	- 480		
Operating voltage range	Vac		160	- 576		
Rated frequency	Hz		50	-60		
Emergency systems - Motor loads or total system	A	1600	2000	2600	3000	
Optional standby systems - Motor loads or total system	A	1600	2000	2600	3000	
Short-circuit withstand/closing and short-time current ratings	kA	See table on following page				
Contact transfer time I-II, II-I Load interrupting time	ms		<"	50		
Operating transfer time I-II, II-I	ms		<5	00		
ATS current draw during transfer / time duration	A / ms	50-65	50-65 <70			
Suitable for applications		Utility - Utility				
		Utility - Generator				
ATS-Bypass orientation			Bottom	and Top		



Cat CBS Series Withstand and Close-on Ratings (WCR) and Short-time Ratings (STR)

		Coordinated fuse ratings Coordinated breaker ratings				tings Coordinated breaker ratings		şs	Time-based	l ratings	Short-time	ratings					
ATS frame	ATS rating	Transition types	480V Max withstand	Class	Max fuse size	240V Max withstand	Max breaker size	480V Max withstand	Max breaker size	480V Max withstand	Time- period	480V Max withstand	Time- period				
			100kA1	Class L	2000A			100kA1	1200A	50kA	0.1 sec						
R4B	100- 1200A	OT, DT	200kA1	Class J or T	800A	200kA1	1600A	CE1-41	10004	CELA	0.05	50kA ¹	0.5 sec				
		200kA1	Class L	1200A		65KA.						65KA' 1600A	65KA' 1600A	65KA	sec		
R5B	1600- 3000A	OT, DT, CT	200kA	Class L	4000A	100kA	no max	100kA	no max	100kA	0.05 sec	65kA	0.5 sec				

1. 3-phase applications only



CBS Series Testing and Standards Compliance

Description	Standard
UL, cUL listing	UL 1008
Conducted and radiated emissions	CISPR 11:2009, Class A
ESD immunity test	IEC/EN 61000-4-2 Class B
Radiated RF, electromagnetic field immunity test	IEC/EN 61000-4-3 10 V/m
Electrical fast, transient/burst immunity test	IEC/EN 61000-4-4
Surge immunity test	IEC/EN 61000-4-5 0.5 to 2 kV
Conducted immunity test	IEC/EN 61000-4-6
Voltage dips and interruption immunity	IEC/EN 61000-4-11
Harmonic voltage immunity test	IEC/EN 6100-4-13

CBS Series AL/CU UL Listed Solderless Screw-	Type Terminals for External Power Connections
--	--

Model	Amperage	Cables per phase & neutral	Range of wire sizes			
	100-200	1	6 AWG - 300 kcmil	(14 - 152 mm²)		
	260-400	1/2	1x 4 AWG - 600 kcmil /	(1x 25 - 304 mm ² /		
CBS			2x 1/0 - 250 kcmil	2x 55 - 127 mm²)		
CBSD	600	2	2 AWG - 600 kcmil	(34 - 304 mm²)		
CBSCT	800-1200	4	2 AWG - 600 kcmil	(34 - 304 mm²)		
	1600-3000	8	2 AWG - 600 kcmil	(34 - 304 mm²)		
		8	750 kcmil	(380 mm²)		



Dimensions

100-1200A



1600-3000A*

CBS Series dimensions								
Madal	ATS	Deles	D	imensions, ² in (mr	n)	Reference		
Widdel	Rating (A)	Poles	Height (A)	Width (B)	Depth (C)	figure		
CBS/CBSD	100-1200	2, 3, 4	92 (2336.8)	36.1 (917.0)	37.4 (950.0)	1		
CBS/CBSD/CBSCT	1600-3000	3, 4	77.0 (1955.8)	46.0 (1168.4)	67.0 (1701.8)	2		

Materials and specifi cations are subject to change without notice.

CAT, CATERPILLAR, LET'S DO THE WORK, their respective logos, "Caterpillar Corporate Yellow," the "Power Edge" and Cat "Modern Hex" trade dress as well as corporate and product identity used herein, are trademarks of Caterpillar and may not be used without permission.