

Cat® DE65 GC

Diesel Generator Sets



Standby and Prime: 50 Hz & 60 Hz



Image shown may not reflect actual configuration

Engine Model	Cat® C3.3 Inline 4-stroke Diesel
Bore x Stroke	105.0 mm x 127.0 mm (4.1 in x 5.0 in)
Displacement	3.3 L (201.4 in³)
Compression Ratio	17.25:1
Aspiration	Turbocharged
Fuel Injection System	Inline
Governor	Mechanical

Model	Standby		Prime (SRR)	Emission Strategy
	50 Hz kVA (ekW)	60 Hz kVA (ekW)	50 Hz kVA (ekW)	
DE65 GC	65 (52)	75 (60)	58.5 (46.8)	Low BSFC

PACKAGE PERFORMANCE

Performance	Standby		Prime (SRR)
	50 Hz	60 Hz	50 Hz
Genset power rating	65 kVA	75 kVA	58.5 kVA
Genset power rating with fan @ 0.8 power factor	52 ekW	60 ekW	46.8 ekW
Emissions	Low BSFC		
Performance number	P2506B	P2506A	-
Fuel Consumption			
Fuel tank capacity, L (gal)	103 (27.2)		
100% load with fan, L/hr (gal/hr)	15.3 (4.0)	18.2 (4.8)	13.7 (3.6)
75% load with fan, L/hr (gal/hr)	11.3 (3.0)	13.6 (3.6)	10.1 (2.6)
50% load with fan, L/hr (gal/hr)	7.8 (2.1)	9.5 (2.5)	7 (1.8)
Cooling System¹			
Radiator air flow, m³/min (CFM)	110.4 (3899)	145.8 (5149)	110.4 (3899)
Total coolant capacity, L (gal)	10.2 (2.7)		
Inlet Air			
Max. combustion air intake restriction, kPa (in. water)	8.0 (32.1)		
Combustion air inlet flow rate, m³/min (CFM)	3.9 (138)	4.9 (173)	3.5 (123)
Exhaust System			
Exhaust stack gas temperature, °C (°F)	571 (1060)	564 (1047)	545 (1013)
Exhaust gas flow rate, m³/min (CFM)	10.4 (367)	12.5 (441)	9.4 (332)
Exhaust system backpressure (maximum allowable), kPa (in. water)	10.0 (3.0)	15.0 (4.4)	10.0 (3.0)
Heat Rejection			
Heat rejection to jacket water, kW (BTU/min)	38.0 (2161)	43.0 (2445)	35 (1990)
Heat rejection to alternator, kW (BTU/min)	5.7 (324)	6.0 (341)	5.4 (307)
Heat rejection to atmosphere from engine, kW (BTU/min)	11 (626)	11 (626)	10 (568)
Heat rejection to exhaust (total), kW (BTU/min)	46.0 (2618)	54.0 (3074)	44 (2502)


DE65 GC Diesel Generator Sets

Electric Power



Alternator ²	50 Hz (Standby/Prime)			60 Hz (Standby)				
Voltages	380	415	400	480	440	220	380	240
Motor starting capability @ 30% Voltage Dip, skVA	100	120	111	133	111	111	84	100
Current, Amps	99 / 89	90 / 81	94 / 84	90	98	197	105	179
Temperature Rise, °C	150/40	150/40	150/40	130/40	150/40	150/40	163/27	163/27
Frame Size	A2133L4							
Excitation	S.E							

WEIGHTS & DIMENSIONS



Note: General configuration not to be used for installation. See general dimension drawings for detail.

Length "A" mm (in)	Width "B" mm (in)	Height "C" mm (in)	Dry Weight [#] kg (lb)
1773 (70)	900 (35.4)	1273 (50)	825 (1818)

[#]Weight includes standard generator and integral tank base.

APPLICABLE CODES AND STANDARDS:

AS1359, IEC60034-1, ISO3046, ISO8528, NEMA MG1-33, EAC,CE,UKCA.

Note: Codes may not be available in all model configurations. Please consult your local Cat Dealer representative for availability.

STANDBY: Output available with varying load for the duration of the interruption of the normal source power. Average power output is 70% of the standby power rating. Typical operation is 200 hours per year, with maximum expected usage of 500 hours per year.

PRIME (SRR): Output available with varying load. Average power output is 70% of the prime power rating. Typical peak demand is 100% of prime rated kW with 10% overload capability for emergency use for a maximum of 1 hour in 12. Overload operation cannot exceed 25 hours per year. Maximum run time not to exceed 2000 hours per year.

DEFINITIONS AND CONDITIONS

¹ For ambient and altitude capabilities consult your Cat dealer. Air flow restriction (system) is added to existing restriction from factory.

² Generator temperature rise is based on IEC 60034-1.

RATINGS: Ratings are based on SAE J1349 standard conditions. These ratings also apply at ISO 3046 standard conditions.

LET'S DO THE WORK.™

www.cat.com/electricpower

©2026 Caterpillar All rights reserved.

Materials and specifications are subject to change without notice.

The International System of Units (SI) is used in this publication. CAT, CATERPILLAR, LET'S DO THE WORK, their respective logos, "Caterpillar Corporate Yellow" the "Power Edge" and Cat "Modern Hex" trade dress as well as corporate and product identity used herein, are trademarks of Caterpillar and may not be used without permission.