## Cat® XQP200 Rental Generator Set





Prime 200 kVA (160 kW) 50/60 Hz Switchable EU Stage V

Image shown may not reflect actual configuration.

#### **Specifications**

Frequency	Speed (rpm)	Speed		Prime		Breaker	
(Hz)		Voltage	kVA	kW	Amps (A)	Rating (A)	
		415 / 240 V	200	160	278		
50 1500	400 / 230 V	200	160	289	400		
		380 / 220 V	190	152	289		
60			480 / 277 V	225	180	271	
		440 / 254 V	225	180	295	400	
	1800	380 / 220 V	198	158	301		
		240 / 139 V	N/A	N/A	N/A	NIA	
		220 / 127 V	N/A	N/A	N/A	NA	

Cat® C7.1 Diesel Engine	Metric Imperial (English)		
Configuration	Inline 6-cylinder, 4-Stroke-Cycle, Water Cooled, Diesel		
Bore	105 mm 4.13 in		
Stroke	135 mm	5.31 in	
Displacement	7.01 L	427.8 in <sup>3</sup>	
Aspiration	Turbocharged-Aftercooled (TA)		
Compression Ratio	16.5:1		
Engine rpm	1500 –1800		
Aftercooler Type	ATAAC		
Turbocharger	Twin		
Fuel System	Direct Injection		
Governor Type	Electronic ECM controlled (A6E2)		
Fuel See Fuel Specification Table		cification Table	

LEHX20177-03 1 of 8



#### **Benefits & Features**

#### **Rental-ready Features**

- Dual wall tank base with drag / tie down points and robust skid plate
- · Forklift pockets
- · Externally certified single point lift
- Certified spark arrest system
- 50/60 Hz frequency switch via terminal link
- EMC certified
- Robust busbar connection for lugged cable connection
- AC protected by limit switch on distribution door

#### **Fuel/Emissions Strategy**

· EU Stage V

#### Single-source Supplier

- Factory designed and fully prototype tested with torsional vibration analysis available
- · ISO 9001:2000 compliant facility

#### Cat® C7 ACERT™ Diesel Engine

- Four-stroke diesel engine combines consistent performance and excellent fuel economy with minimum weight
- Electronic ECM control

#### **After Treatment**

- Diesel Emissions Fluid (DEF) Tank located in discharge box, accessible through lockable access door
- DEF tank capacity is sufficient to last more than 24 hrs when fully filled

#### **Cat XQCP Control Panel**

- Fully featured power metering, protective relaying, engine/generator control and monitoring
- Simple user-friendly interface and navigation
- Single point interface for voltage and frequency adjustment

## **Optional Control Panel**

- ComAp InteliGen NTC, Deep Sea 8620, DEIF AGC-4
- Syncronising capabilities
- Motorised breaker
- · Ethernet remote monitoring
- AVR (Automatic Voltage Regulator) R450T comes with DEIF, ComAp or DSE8620 panel selection

#### **Available Options**

- CE socket box with integrated MCB & RCBO protection
- · Syncronising control panel and motorised breaker
- Anti condensation heater 230V AC
- Coolant heater 230V AC
- Permanent Magnet Generator (PMG)
- · Earth leakage detection
- Lube oil sump pump
- Fuel Option Pack Inboard mounted 3-way valve for external fuel connection, electronic fuel gauge and Bund Level Sender
- Battery option 2x 12V 950CCA maintenance-free CAT Batteries
- Battery Isolator Single pole (padlockable)
- · 24V battery charger
- Control Panel noise breakout option
- Drains option Pack Oil and coolant drains piped to baseframe

#### Cat LC5100 Generator

- Designed to match performance and output of Cat diesel engines
- · Coastal insulation protection
- Self (shunt) excitation

#### Integrated Voltage Regulator (IVR-D350)

- Three-phase sensing
- Adjustable Volts-per-Hertz regulation
- Provides precise control, excellent block loading, and constant voltage in the normal operating range

#### **Enclosure**

- Galvanized sheet steel construction
- Two coat polyester powder-coated finish
- 6 access doors for improved service access
- Secure design with safety glass control panel viewing window and padlockable or keylock access doors
- Fuel fill, battery and controls accessible only through lockable access doors

#### **Environmental Considerations**

- 110% spill containment of all on-board engine fluids and bund level alarm
- · Low noise enclosure

#### **Cat Connect**

· Fleet management and asset tracking\*

\*Subject to local certifications

LEHX20177-03 2 of 8



#### Standard Equipment

#### Generator

- LC5114F frame; 3-phase random wound, 12 lead, self- excited, 2/3 pitch
- Coastal insulation protection (CIP)

#### Cat® C7 Diesel Engine

- · Twin turbocharged, air-to-air aftercooler
- Electronic ECM control

#### **After Treatment**

- Engine Mounted Clean Emissions Module (CEM)
- Diesel Emissions Fluid (DEF) Tank located in discharge box, accessible through lockable access door

#### Air Filter

 High Efficiency two stage air cleaner, with dust cup and service indicator

#### **Cooling System**

- · Package mounted radiator with vertical air discharge
- · High ambient performance
- Fully guarded pusher fan
- · Low coolant level shutdown
- · 50% glycol mix with corrosion inhibitor

#### **Charging System**

 Charging alternator; 24V, heavy duty with integral regulator and belt guards

#### **Starting System**

Single 24V electric starting motor

#### **Fuel System**

- 24 hr dual wall fuel tank (based on 75% Prime load)
- · Internal fuel fill
- · Engine mounted primary and secondary fuel filter
  - o Primary filter (10 micron) with integral water separator (330 ml capacity)
  - o Secondary filter (4 micron)
- · Automatic onboard priming pump
- Mechanical fuel gauge

#### **Control Panel**

- · XQCP set mounted digital controller
- 50/60 Hz frequency switch (via terminal link)
- D350 Voltage Regulator
- Panel & enclosure mounted emergency stop

#### **Distribution System**

- Separate robust steel enclosures for control & distribution sections
- Distribution door protected with 24V DC shunt trip safety switch
- 4 pole, 400A main circuit breaker
- Two-wire remote start/stop terminals and AC aux power connection for rapid starting

#### **Mounting System**

- Heavy duty steel baseframe with integral fuel tank (dual wall)
- Provides 110% spill containment including all on-board fluids
- · Forklift pockets
- · Skid plates with drag points
- Generator set soft mounted using captive vibration mounts

#### **Enclosure**

- Sound attenuating, galvanised sheet steel enclosure with exceptional noise reduction performance
- Interior walls, ceilings and ducts insulated with precision cut noise insulating materials
- Sealed quarter-turn compression latches with key or padlock capabilities
- External side-mounted dual point lifting frame for improved hook access
- · Powder coated with Cat Rental Power decals

#### **Exhaust System**

- · Certified spark arresting system
- · Outlet box mounted with vertical discharge

#### **Lube Oil System**

- On-engine primary and secondary oil filters, dipstick and oil filler
- · Closed crankcase breather
- · 500 hour oil change requirement

#### General

- Factory Tested
- Full manufacturer's warranty, O&M manuals

LEHX20177-03 3 of 8



## **Fuel Specifications**

Specification Standard	Grade Class	Fuel Description
EU Stage V specifies Ultra Low Sulphur Diesel		Ultra Low Sulphur Diesel Only (ULSD) ULSD with a maximum fuel sulphur level of either 15 or 20 ppm1 is required in all diesel applications using a diesel particulate filter (DPF and DOC). Bio-diesel fuel may be used up to B20 (80% standard ULSD with 20% bio-fuel dilution by volume), provided an appropriate approved additive is used.

## Oil Specifications

Specification Standard	Oil Description		
EU Stage V Recommended oil 15W-40 CK-4 1E1867F	Minimum spec 15W-40 CJ-4 1E1867E		

## **DEF Specifications**

Specification Standard	DEF Description		
EU Stage V DEF Requirements ISO22241-1	European automotive fuel (DERV)		

LEHX20177-03 4 of 8



## **Technical Data**

Cat® Generator			
Frame size LC5114F			
Pitch	2/3		
No. of poles	4		
Excitation	Static regulated, brushless, self excited		
Number of bearings	Single bearing, close coupled		
Insulation	Class H		
Temperature rise	125/40°C		
Enclosure	Drip proof IP23		
Overspeed capability — % of rated	25%		
Voltage regulator	3-phase sensing with adjustable volts per hertz		
Voltage regulation	Less than ± 0.5%		
Wave form deviation Telephone Influence Factor (TIF) Harmonic Distortion (THD)	Less than 2% Less than 2%		

Cat Generator Set			
	TMI Performance No. Units	Prime — 50 Hz T6316	Prime — 60 Hz T4902
Power Rating	kVA (kW)	200 (160)	225 (180)
Performance Specification			
Lubricating System Oil pan capacity	L (gal)	17.1	(4.5)
Fuel System Fuel consumption — 100% Load 75% Load 50% Load Fuel tank capacity Running time @ 75% rating	L/hr (gal/hr) L/hr (gal/hr) L/hr (gal/hr) L (gal) Hr	43.4 (11.5) 32.4 (8.6) 22.1 (5.8) 822 (217) 25	54.3 (14.3) 39.9 (10.5) 27.3 (7.2) 822 (217) 20
After Treatment* DEF Tank Capacity	L (gal)	32 (8	8.45)
Cooling System Ambient capability Engine & radiator coolant capacity Engine coolant capacity	°C (°F) L (gal) L (gal)	40 (104) 33 (8.7) 13.2 (3.5)	40 (104) 33 (8.7) 13.2 (3.5)
Air Requirements Combustion air flow	m³/min (cfm)	12.6 (444.8)	14.2 (501.3)
Exhaust System Exhaust flow at rated — dry exhaust Exhaust temperature at rated kW	m³/min (cfm) °C (°F)	13.8 (487) 480 (896)	16.8 (593) 480 (896)

<sup>\*</sup>DEF consumption is on average approximately 4% of the fuel consumption.

LEHX20177-03 5 of 8



## Technical Data (continued)

Cat Generator Set				
	TMI Performance No. Units	Prime — 50 Hz T6316	Prime — 60 Hz T4902	
Noise Rating (with enclosure) **				
Sound Power*	dB(A)	93.8	97.0	
@ 7 meters @ 75% load	dB(A)	64.6	TBC	
@ 7 meters @ 100% load	dB(A)	66.1	TBC	
@ 1 meters @ 75% load	dB(A)	75.1	TBC	
@ 1 meter @ 100% load	dB(A)	76.1	TBC	
Emissions data at 100% Load				
Nox	g/hp-hr	TBC	TBC	
CO	g/hp-hr	TBC	TBC	
HC	g/hp-hr	TBC	TBC	
PM	g/hp-hr	TBC	TBC	

<sup>\*\*</sup>Guaranteed sound power as per 2000/14/EC.

For full Engine & Emissions data please refer to TMI using the engine performance no.

Dimensions			
	Length — mm (in)	Width — mm (in)	Height — mm (in)
Generator Set	4085 (161)	1420 (56)	2350 (93)

Weight		
	Weight — kg (lb)	
Lube Oil & Coolant — Empty Fuel Tank	3651 (8049)	
Full Fuel Tank	4487 (9892)	


Sockets	15A	16A	32A	50A	63A	125A
CEE Form*	_	2x1ph+N+E	2x3ph+N+E	_	1x3ph+N+E	1x3ph+N+E

<sup>\*</sup>Busbar connection is standard. Distribution sockets are optional.

LEHX20177-03 6 of 8



# Layout for General Dimensions Dimensions in millimeters (inches)




LEHX20177-03 7 of 8



## **Control Panel and Power Distribution Layout**

Item	Description	
1	Steel enclosure with hinged, lockable door (not shown)	
2	XQCP digital genset controller	
3	Emergency Stop button	
4	Alarm	
5	Service tool connector	
6	Circuit breaker. 4-pole molded case, 630A	
7	Main bus connection (bus bars with 14 mm holes)	
8	Micro safety switch for bus bar door	
9	Manual holder	
10	Emission system failure lamp	
11	Low DEF level lamp	



#### **Rating Definitions and Conditions**

**Designed to Meet Specifications:** ISO 8528, EN 12601, EN 60204-1, ISO 3046, IEC 60034.

**Ratings** are based on SAE J1349 standard conditions. These ratings also apply at ISO3046 standard conditions.

**Prime** — Output available with varying load for an unlimited time. Average power output is 70% of the prime power rating. Typical peak demand is 100% of prime rated ekW with 10% overload capability for emergency use for a maximum of 1 hour in 12. Overload operation cannot exceed 25 hours per year.

**Fuel rates** are based on fuel oil of 35° API [16°C (60°F)] gravity having an LHV of 42 780 kJ/kg (18,390 Btu/lb) when used at 29°C (85°F) and weighing 838.9 g/liter (7.001 lbs/U.S. gal).

Additional ratings may be available for specific customer requirements, contact your Cat representative for details. For information regarding low sulfur fuel and biodiesel capability, please consult your Cat dealer.