

Cat® D250 GC

Diesel Generator Sets



Standby : 60 Hz



Image shown may not reflect actual configuration

Engine Model	Cat® C9 In-line 6, 4-cycle Diesel
Bore x Stroke	112 mm x 149 mm (4.4 in x 5.9 in)
Displacement	8.8 L (538 in³)
Compression Ratio	16.3:1
Aspiration	Turbocharged Air-to-Air Aftercooled
Fuel Injection System	HEUI
Governor	Electronic ADEM™ A4 - G3 Class* capable

Model	Standby	Emission Strategy
D250 GC	250 ekW, 312.5 kVA	EPA Certified for Stationary Emergency Application

PACKAGE PERFORMANCE

Performance	Standby
Frequency	60 Hz
Genset Power Rating	312.5 kVA
Genset power rating with fan @ 0.8 power factor	250 ekW
Emissions	EPA TIER 3
Performance Number	DM8501
Fuel Consumption	
100% load with fan, L/hr (gal/hr)	73.3 (19.4)
75% load with fan, L/hr (gal/hr)	58.8 (15.5)
50% load with fan, L/hr (gal/hr)	43.8 (11.6)
25% load with fan, L/hr (gal/hr)	27.4 (7.3)
Cooling System¹	
Radiator air flow restriction (system), kPa (in water)	0.12 (0.48)
Radiator air flow, m³/min (cfm)	497 (17551)
Engine coolant capacity, L (gal)	14 (3.69)
Radiator coolant capacity, L (gal)	25 (6.6)
Total coolant capacity, L (gal)	45 (11.88)
Inlet Air	
Combustion air inlet flow rate, m³/min (cfm)	23.83 (841.5)
Max. Allowable Combustion Air Inlet Temp, °C (°F)	49 (120)
Exhaust System	
Exhaust stack gas temperature, °C (°F)	460 (860)
Exhaust gas flow rate, m³/min (cfm)	63.6 (2246)
Exhaust system back pressure (maximum allowable), kPa (in. water)	10.0 (40.0)
Heat Rejection	
Heat rejection to jacket water, kW (Btu/min)	104 (5928)
Heat rejection to exhaust (total), kW (Btu/min)	277 (15772)
Heat rejection to aftercooler, kW (Btu/min)	82 (4686)
Heat rejection to atmosphere from engine, kW (Btu/min)	18 (1004)
Heat rejection from alternator, kW (Btu/min)	20 (1120)
Emissions (Nominal)²	
NOx, mg/Nm³ (g/hp-hr)	1637.5 (3.14)
CO, mg/Nm³ (g/hp-hr)	323.2 (0.68)
HC, mg/Nm³ (g/hp-hr)	71.2 (0.17)
PM, mg/Nm³ (g/hp-hr)	63.7 (0.16)


D250 GC Diesel Generator Sets

Electric Power



Alternator ³			
Voltages	480V	208	600V
Motor starting capability @ 30% Voltage Dip, skVA	567	544	1006
Current, Amps	375.9	867.4	300.7
Frame Size	M2754L4	M2774L4	M2754L4
Excitation	S.E	S.E	AREP
Temperature Rise, °C	105	105	105

WEIGHTS & DIMENSIONS – OPEN SET



FUEL TANK CAPACITY

Tank Design	Total Capacity L (gal)	Useable Capacity L (gal)
Integral	2270 (600)	2059 (554)

Base	Length "A" mm (in)	Width "B" mm (in)	Height "C" mm (in)	Generator Set Weight kg (lb)
Skid (Wide Base)	3950 (155.5)	1440 (56.7)	1706 (67.2)	2415 (5324.2)
Integral Tank Base	3950 (155.5)	1430 (56.3)	2202 (86.7)	3055 (6735.1)

Note: General configuration not to be used for installation. See general dimension drawings for detail.

APPLICABLE CODES AND STANDARDS:

CSA C22.2 No 100-04, UL142, UL489, UL869, cUL/UL2200, NFPA 37, NFPA 70, NFPA 99, NFPA 110, IBC, IEC60034-1, ISO 3046, ISO 8528, NEMA MG 1-33.

Note: Codes may not be available in all model configurations. Please consult your local Cat Dealer representative for availability.

STANDBY: Output available with varying load for the duration of the interruption of the normal source power. Average power output is 70% of the standby power rating. Typical operation is 200 hours per year, with maximum expected usage of 500 hours per year.

RATINGS: Ratings are based on SAE J1349 standard conditions. These ratings also apply at ISO3046 standard conditions.

FUEL RATES: Based on fuel oil of 35° API [16° C (60° F)] gravity having an LHV of 42 780 kJ/kg (18,390 Btu/lb) when used at 29° C (85° F) and weighing 838.9 g/litre (7.001 lbs/U.S. gal.). Additional ratings may be available for specific customer requirements, contact your Caterpillar representative for details. For information regarding Low Sulfur fuel and Biodiesel capability, please consult your Cat dealer.

DEFINITIONS AND CONDITIONS

¹ For ambient and altitude capabilities consult your Cat dealer. Air flow restriction (system) is added to existing restriction from factory.

² Emissions data measurement procedures are consistent with those described in EPA CFR 40 Part 89, Subpart D & E and ISO8178-1 for measuring HC, CO, PM, NOx. Data shown is based on steady state operating conditions of 77° F, 28.42 in HG and number 2 diesel fuel with 35° API and LHV of 18,390 BTU/lb. The nominal emissions data shown is subject to instrumentation, measurement, facility and engine to engine variations. Emissions data is based on 100% load and thus cannot be used to compare to EPA regulations which use values based on a weighted cycle.

³ UL 2200 Listed packages may have oversized generators with a different temperature rise and motor starting characteristics. Generator temperature rise is based on a 40° C ambient per NEMA MG1-32.

* Governing Class capability as per ISO8528-5. Consult your local Cat dealer for configuration and site specific transient performance classification.

www.cat.com/electricpower
©2025 Caterpillar
All rights reserved.

Materials and specifications are subject to change without notice. The International System of Units (SI) is used in this publication.

CAT, CATERPILLAR, LET'S DO THE WORK, their respective logos, "Caterpillar Corporate Yellow", the "Power Edge" and Cat "Modern Hex" trade dress as well as corporate and product identity used herein, are trademarks of Caterpillar and may not be used without permission.